





- NOTES:
- MATERIAL: ALL MATERIALS ARE RoHS COMPLIANT PER EU DIRECTIVE 2011/65/EU
HOUSING: THERMOPLASTIC PBT, UL FLAMMABILITY RATING 94V-0, BLACK
CONTACT: COPPER ALLOY PLATED WITH GOLD FLASH OVER NICKEL
DUST CAP: SILICONE RUBBER, BLACK
FRONT HOUSING: ZINC ALLOY PLATED WITH CHROME OR THERMOPLASTIC PBT, SEE BELOW TABLE
HEX NUT: STEEL PLATED WITH NICKEL OR THERMOPLASTIC PBT, SEE BELOW TABLE
 - ELECTRICAL CHARACTERISTICS:
CURRENT RATING: 10A
OPERATING VOLTAGE: 500V AC MAXIMUM
DIELECTRIC WITHSTANDING VOLTAGE: 2500V DC
CONTACT RESISTANCE: 5.0mΩ MAXIMUM.
 - RECOMMENDED PANEL THICKNESS: 2.5 (0.098) TO 3.0 (0.118).
 - ENVIRONMENTAL PROTECTION: IP67 PER IEC 60529 IN THE MATED CONDITION.

ORDERING CODE: M R D - B X 0 3 - L 1 3 - 0 0 0

SERIES
CONTACT SIZE & MECHANISM
B=1.5mm & LATCH LOCK
HOUSING ORIENTATION & CONTACT TYPE
G=FEMALE METAL HOUSING & PIN CONTACT
J=FEMALE PLASTIC HOUSING & PIN CONTACT
NUMBER OF CONTACTS
03=THREE CONTACTS

SPECIALS
000=STANDARD
MOUNTING/COVER OPTIONS
3= PANEL MOUNT WITH DUST COVER
CONTACT TERMINATION TYPE
L1=SOLDER CUP

CONNECTOR PART NUMBER	FRONT HOUSING MATERIAL	HEX NUT MATERIAL
MRD-BG03-L13-000	ZINC / CHROME	STEEL / NICKEL
MRD-BJ03-L13-000	PBT	PBT

UNLESS SPECIFIED OTHERWISE	DRAWN K.XIONG	SEP28/17
PRIMARY UNITS MILLIMETERS	CHECKED K.LAMBIE	MAR14/18
SECONDARY INCHES	M.E. APP'D	
REFERENCE IN PARENTHESES	Q.A. APP'D	
GENERAL TOLERANCES	DWG APP'D A.GREEN	MAR14/18
1 DECIMAL PLACE ±0.25	ENG. REL. NO.	
2 DECIMAL PLACES ±0.15	REF. EAR 14575	
3 DECIMAL PLACES ±0.05	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING
ANGULAR DEGREES		

Amphenol Canada Corp. Commercial Products		
MRD SERIES RUGGED CONNECTOR, FEMALE WITH 3 PIN CONTACTS, LATCH LOCK, PANEL MOUNT WITH DUST COVER, IP67 RATING, RoHS COMPLIANT		
DWG NO.	P-MRD-BX03-L13-000	REV C
CODE ID NO. 03554	DWG SIZE X	SCALE XX:1
SHEET 1 OF 1		