

MATERIAL:

CAGE:
COPPER ALLOY

PLATING OPTION X=2:
2.54um MIN. NICKEL


PLATING OPTION X=3:
3.81um MIN. MATTE TIN
OVER 1.27um MIN. NICKEL.

GASKET:
CONDUCTIVE ELASTOMER
FLAMMABILITY RATING
UL94-V0


PACKAGING:
TRAY PACKAGING

TEMPERATURE RANGE:
-40C TO +85C


REVISIONS				
REV.	ECN/E-R	DESCRIPTION	DATE	APPROVED
A		PROPOSAL	MAR26/09	
B		UPDATED	JUL14/09	
C		B-B APPLICATION SPECIFIED	AUG14/09	



P/N: U77-A641M-X081 SHOWN



P/N: U77-A241M-X081 SHOWN



P/N: U77-A441M-X081 SHOWN

AMPHENOL PART NUMBER CONFIGURATION

U77 - A X 4 1 M - X 0 8 1

PACKAGING
1 = TRAY PACKAGING

PLATING
2 = NICKEL PLATING
3 = MATTE TIN PLATING

NUMBER OF PORTS
2 = 2 PORTS
4 = 4 PORTS
6 = 6 PORTS


NOTE:

PRODUCT COMPLIES WITH SFF 8433 SPEC.

DO NOT SCALE DRAWING





THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: DECIMALS ANGLES X.X ± 0.38 ± 1° X.XX ± 0.25		APPROVALS		DATE	Amphenol Canada Corp.		
		DRAWN	ChigowX	MAR04/09			
		DESIGNED			1XN SFP+ CAGE ASSEMBLY WITH ELASTOMERIC GASKET		
		CHECKED	J.SI	MAR26/09			
MATERIAL AND FINISH SEE NOTE 1		QA APPD			SIZE A3 DWG. NO. P-U77-AX41M-X081 REV. C		
REF.		IE APPD					
CODE IDENT. NO. 03554		DWG APPD	A.G.	MAR26/09	SCALE 2:1	PROJECT	SHEET 1 OF 10



PART NUMBER	DIM "C"	DIM "D"
U77-A241M-X091	29.70	34.25
U77-A441M-X091	58.20	62.75
U77-A641M-X091	86.70	91.25


REVISIONS				
REV.	ECN/E-R	DESCRIPTION	DATE	APPROVED
A		PROPOSAL	MAR26/09	
B		UPDATED	JUL14/09	
C		B-B APPLICATION SPECIFIED	AUG14/09	




DO NOT SCALE DRAWING

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: DECIMALS ANGLES X.X ± 0.38 ± 1° X.XX ± 0.25		APPROVALS		DATE	Amphenol Canada Corp.		
		DRAWN	ChigowX	MAR04/09			
MATERIAL AND FINISH		CHECKED		J.SI	MAR26/09	1XN SFP+ CAGE ASSEMBLY WITH ELASTOMERIC GASKET	
SEE NOTE 1		QA APPD					
REF.		IE APPD				SIZE A3	DWG. NO. P-U77-AX41M-X081
CODE IDENT. NO.		DWG APPD		A.G.	MAR26/09	SCALE 2:1	PROJECT
03554							SHEET 3 OF 10



		REVISIONS		
REV.	ECN/E-R	DESCRIPTION	DATE	APPROVED
A		PROPOSAL	MAR26/09	
B		UPDATED	JUL14/09	
C		B-B APPLICATION SPECIFIED	AUG14/09	



RECOMMENDED PCB DESIGN FOR SINGLE SIDE MOUNTING (P/N U77-A241M-X081)

DO NOT SCALE DRAWING


THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE:		APPROVALS		DATE		Amphenol Canada Corp.			
DECIMALS ANGLES X.X ± 0.38 ± 1° X.XX ± 0.25		DRAWN ChigowX		MAR04/09		TITLE 1XN SFP+ CAGE ASSEMBLY WITH ELASTOMERIC GASKET			
		DESIGNED							
MATERIAL AND FINISH SEE NOTE 1		CHECKED J.SI		MAR26/09					
REF.		QA APP'D							
		IE APP'D				SIZE A3	DWG. NO. P-U77-AX41M-X081	REV. C	
CODE IDENT. NO. 03554		DWG APP'D A.G.		MAR26/09		SCALE 2:1	PROJECT	SHEET 5 OF 10	

NOTES:

1. DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
2. PADS AND VIAS ARE CHASSIS GROUND.
3. THRU-HOLES, PLATING OPTIONAL.
4. SEE DRAWINGS P-UX76-A20-X00XX FOR CONNECTOR LAYOUT.

		REVISIONS		
REV.	ECN/E-R	DESCRIPTION	DATE	APPROVED
A		PROPOSAL	MAR26/09	
B		UPDATED	JUL14/09	
C		B-B APPLICATION SPECIFIED	AUG14/09	



**RECOMMENDED PCB DESIGN
FOR BELLY TO BELLY MOUNTING
(P/N U77-A241M-X081)**


DO NOT SCALE DRAWING

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: DECIMALS ANGLES X.X ± 0.38 ± 1 ° X.XX ± 0.25 MATERIAL AND FINISH SEE NOTE 1 REF.		APPROVALS		DATE		Amphenol Canada Corp.			
		DRAWN ChigowX		MAR04/09					
		DESIGNED				TITLE 1XN SFP+ CAGE ASSEMBLY WITH ELASTOMERIC GASKET			
		CHECKED J.SI		MAR26/09					
QA APPD									
		IE APP'D				SIZE A3	DWG. NO. P-U77-AX41M-X081	REV. C	
CODE IDENT. NO. 03554		DWG APP'D A.G.		MAR26/09		SCALE 3:1	PROJECT	SHEET 6 OF 10	

NOTES:
1. DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
2. PADS AND VIAS ARE CHASSIS GROUND.
3. THRU-HOLES, PLATING OPTIONAL.
4. SEE DRAWINGS P-UX76-A20-X00XX FOR CONNECTOR LAYOUT.

REVISIONS				
REV.	ECN/E-R	DESCRIPTION	DATE	APPROVED
A		PROPOSAL	MAR26/09	
B		UPDATED	JUL14/09	
C		B-B APPLICATION SPECIFIED	AUG14/09	



**RECOMMENDED PCB DESIGN
FOR SINGLE SIDE MOUNTING
(P/N U77-A441M-X081)**


DO NOT SCALE DRAWING

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: DECIMALS ANGLES X.X ± 0.38 ± 1° X.XX ± 0.25 MATERIAL AND FINISH SEE NOTE 1 REF. CODE IDENT. NO. 03554		APPROVALS	DATE	Amphenol Canada Corp.	
		DRAWN ChigowX	MAR04/09	1XN SFP+ CAGE ASSEMBLY WITH ELASTOMERIC GASKET	
		DESIGNED			
		CHECKED J.SI	MAR26/09		
		QA APPD		SIZE A3	DWG. NO. P-U77-AX41M-X081
		IE APPD		SCALE 1:1	PROJECT
		DWG APPD A.G.	MAR26/09	SHEET 7 OF 10	REV. C

- NOTES:
1. DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
 2. PADS AND VIAS ARE CHASSIS GROUND.
 3. THRU-HOLES, PLATING OPTIONAL.
 4. SEE DRAWINGS P-UX76-A20-X00XX FOR CONNECTOR LAYOUT.

REVISIONS				
REV.	ECN/E-R	DESCRIPTION	DATE	APPROVED
A		PROPOSAL	MAR26/09	
B		UPDATED	JUL14/09	
C		B-B APPLICATION SPECIFIED	AUG14/09	



**RECOMMENDED PCB DESIGN
FOR BELLY TO BELLY MOUNTING
(P/N U77-A441M-X081)**


DO NOT SCALE DRAWING

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: DECIMALS ANGLES X.X ± 0.38 ± 1° X.XX ± 0.25		APPROVALS	DATE	Amphenol Canada Corp.	
		DRAWN ChigowX	MAR04/09		
MATERIAL AND FINISH SEE NOTE 1		DESIGNED		1XN SFP+ CAGE ASSEMBLY WITH ELASTOMERIC GASKET	
		CHECKED J.SI	MAR26/09		
REF.		QA APPD		SIZE A3	
		IE APPD			
CODE IDENT. NO. 03554		DWG APPD A.G.	MAR26/09	SCALE 2:1	PROJECT P-U77-AX41M-X081
				SHEET 8 OF 10	REV. C


- NOTES:
1. DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
 2. PADS AND VIAS ARE CHASSIS GROUND.
 3. THRU-HOLES, PLATING OPTIONAL.
 4. SEE DRAWINGS P-UX76-A20-X00XX FOR CONNECTOR LAYOUT.

REVISIONS				
REV.	ECN/E-R	DESCRIPTION	DATE	APPROVED
A		PROPOSAL	MAR26/09	
B		UPDATED	JUL14/09	
C		B-B APPLICATION SPECIFIED	AUG14/09	



- NOTES:
1. DATUM AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
 2. PADS AND VIAS ARE CHASSIS GROUND.
 3. THRU-HOLES, PLATING OPTIONAL.
 4. SEE DRAWINGS P-UX76-A20-X00XX FOR CONNECTOR LAYOUT.

REVISIONS				
REV.	ECN/E-R	DESCRIPTION	DATE	APPROVED
A		PROPOSAL	MAR26/09	
B		UPDATED	JUL14/09	
C		B-B APPLICATION SPECIFIED	AUG14/09	



DO NOT SCALE DRAWING

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT PERMISSION FROM AMPHENOL CANADA CORP.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: DECIMALS ANGLES X.X ± 0.38 ± 1° X.XX ± 0.25		APPROVALS	DATE	Amphenol Canada Corp.	
		DRAWN ChigowX	MAR04/09		
		DESIGNED		1XN SFP+ CAGE ASSEMBLY WITH ELASTOMERIC GASKET	
		CHECKED J.SI	MAR26/09		
MATERIAL AND FINISH SEE NOTE 1		QA APPD			
REF.		IE APPD		SIZE A3	DWG. NO. P-U77-AX41M-X081
CODE IDENT. NO. 03554		DWG APPD A.G.	MAR26/09	SCALE 3:2	PROJECT
				SHEET 10 OF 10	REV. C