





Rev	AWO #	Description	Date	Appr
-		RELEASED	3/29/05	

APPROVED: _____ TITLE: _____
 DATE: _____



PCB LAYOUT



Positions: 10, 14, 16, 20, 24, 26, 30, 34, 40, 50, 60, 64
 A = .100 [2.54] x No. of Spoces + .860 [21.84]
 B = .100 [2.54] x No. of Spoces + .460 [11.68]
 C = .100 [2.54] x No. of Spoces

SPECIFICATIONS:
Material:
 Insulator: PBT, rated UL 94V-0
 Insulator color: Black
 Contacts: Brass
 Plating:
 Gold flash over Nickel underplate overall
Electrical:
 Operating voltage: 250 VAC max
 Current rating: 3 Amps max
 Contact resistance: 20 mohms max
 Insulation resistance: 5,000 Mohms min @ 500 VDC
 Dielectric withstanding voltage: 1,000 VAC for 1 minute
Temperature Rating:
 Operating temperature: -55°C to +105°C
Environmental:
 Lead free, RoHS compliant
 Recommended soldering temp: 230°C for 5 seconds

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		TITLE	
X .10 ±.10	ØXX ±.015	LATCHED BOX HEADER, VERTICAL, SHORT EJECTOR LATCHES	
.XX ±.020	ØXXX ±.015	909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
.XXX ±.015	ØXXXX ±.010	ADAM TECH	
APPROVALS	DATE	909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
DRAWN	SS	3/29/05	
CHECKED			
APPROVED			
SIZE	PART NO.	MHR-XX-VUAS	
X			
REF:	SCALE:	NTS	
	SHEET	1 OF 2	