



## E7022BF004 Product Details

[Share](#) | [Print](#) | [Email](#)


**E7022BF004**  
(1-1423170-0)

TE Internal Number: 1-1423170-0

**Active**

### Time Delay Relays

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- 7000 Electropneumatic Timing - Nuclear Qualified Series
- Input Voltage = 240 VAC
- Contact - Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Rating = 10A @ 120 VAC
- Mounting Options = Mounting Holes, Panel Mount

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
[Request Sample](#)
[Find Similar Products](#)
[Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- [Nuclear E7000 Series 2-Pole Timing Relay](#) (PDF, English)

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Series = 7000 Electropneumatic Timing - Nuclear Qualified
- Termination Type = Screw Terminal

#### Electrical Characteristics:

- Input Voltage (VAC) = 240
- Contact Rating = 10A @ 120 VAC

#### Contact Features:

- Mounting Options = Mounting Holes, Panel Mount
- Mode of Operation = Off-Delay
- Delay Time = 1 minute to 10 minutes
- Type of Control = Knob
- Repeatability, Max. = ± 10%
- Approx. Dimensions (L x W x H) (mm [in]) = 82.55 x 78.49 x 107.95 [3.252 x 3.092 x 4.253]

#### Configuration Features:

- [Contact - Arrangement](#) = 2 Form C, DPDT, 2 C/O
- Multiple Timing Ranges = Without

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

#### Conditions for Usage:

- Temperature Range (°C) = 21 - 40

#### Other:

- Brand = Agastat

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

