

## E7014PD004 Product Details

[Share](#) | [Print](#) | [Email](#)


**E7014PD004**  
(1423173-4)

TE Internal Number: 1423173-4

 [Active](#)

### Time Delay Relays

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- 7000 Electropneumatic Timing - Nuclear Qualified Series
- Input Voltage = 125 VDC
- Contact - Arrangement = 4 Form C, 4PDT, 4 C/O
- Contact Rating = 1A @ 125 VDC
- Mounting Options = Mounting Holes, Panel Mount

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

Documentation & Additional Information	
<p><b>Product Drawings:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Catalog Pages/Data Sheets:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Product Specifications:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Application Specifications:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul> <p><b>Instruction Sheets:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">Nuclear E7000 Series 4-Pole Timing Relay</a> (PDF, English)</li> </ul> <p><b>CAD Files:</b></p> <ul style="list-style-type: none"> <li>• None Available</li> </ul>	<p><b>Additional Information:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">Product Line Information</a></li> </ul> <p><b>Related Products:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">Tooling</a></li> </ul>

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p><b>Product Type Features:</b></p> <ul style="list-style-type: none"> <li>• Series = 7000 Electropneumatic Timing - Nuclear Qualified</li> <li>• Termination Type = Screw Terminal</li> </ul> <p><b>Electrical Characteristics:</b></p> <ul style="list-style-type: none"> <li>• Input Voltage (VDC) = 125</li> <li>• Contact Rating = 1A @ 125 VDC</li> </ul> <p><b>Contact Features:</b></p> <ul style="list-style-type: none"> <li>• Mounting Options = Mounting Holes, Panel Mount</li> <li>• Mode of Operation = On-Delay</li> <li>• Delay Time = 10 seconds to 100 seconds</li> <li>• Type of Control = Knob</li> <li>• Repeatability, Max. = ± 10%</li> <li>• Approx. Dimensions (L x W x H) (mm [in]) = 82.55 x 84.33 x 147.83 [3.252 x 3.322 x 5.824]</li> </ul>	<p><b>Configuration Features:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">Contact - Arrangement</a> = 4 Form C, 4PDT, 4 C/O</li> <li>• Multiple Timing Ranges = Without</li> </ul> <p><b>Industry Standards:</b></p> <ul style="list-style-type: none"> <li>• <a href="#">RoHS/ELV Compliance</a> = Not ELV/RoHS compliant</li> <li>• <a href="#">Lead Free Solder Processes</a> = Not relevant for lead free process</li> </ul> <p><b>Conditions for Usage:</b></p> <ul style="list-style-type: none"> <li>• Temperature Range (°C) = 21 - 40</li> </ul> <p><b>Other:</b></p> <ul style="list-style-type: none"> <li>• Brand = Agastat</li> </ul>

### Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

### Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

