

# WIRE MANAGEMENT PRODUCTS

## FLEXIBLE, LIQUID-TIGHT PVC TUBING

FNT

UL RECOGNIZED  
CSA CERTIFIED

### CHOOSE FLEXIBLE LIQUID-TIGHT PVC TUBING FOR:

- Resistance to Oil, Water, Corrosion and Ultraviolet Light
- Flexing/Vibration
- Protection from Stretching, Pulling or Tangling
- Uses Alpha Liquid-Tight Connectors SLC or RLC



### ALPHA'S NEW FLEXIBLE LIQUID-TIGHT PVC TUBING:

(FNT) system of wire management products for electronic and electrical wire protection provides maximum flexibility and can be used in extremely tight quarters. Excellent for general applications where maximum flexibility is required. Ideal in areas where movement, vibration or flexing is a problem.

162

### FLEXIBLE LIQUID-TIGHT PVC TUBING APPLICATIONS:

- Fiber Optic Cable Protection
- Wire Harness Protection
- Flexible Cable Applications



### CHARACTERISTICS

#### OPERATING TEMPERATURE:

- 70°C (UL)
- -18°C to 60°C (CSA)

#### COLOR DESCRIPTION:

- All Standard Package: Black

#### CHEMICAL PROPERTIES:

- Resists Corrosion, Oil and Water
- UV Resistant

### SPECIFICATIONS

- UL Recognized
- CSA Certified (except for 1/4" size)

 **Recognized Component**  
Underwriters Laboratories Inc.

 **Certified**  
Canadian Standards Association

Alpha Part No.	Trade Size Inches	Outside Diameter				Inside Diameter				Standard Put-Up Ft.
		Minimum Inches	Maximum mm	Minimum Inches	Maximum mm	Minimum Inches	Maximum mm	Minimum Inches	Maximum mm	
FNT-1/4	1/4	0.560	14,2	0.575	14,6	0.385	9,78	0.405	10,3	25, 100
FNT-3/8	3/8	0.690	17,5	0.710	18,0	0.484	12,3	0.504	12,8	25, 100
FNT-1/2	1/2	0.820	20,8	0.840	21,3	0.622	15,8	0.642	16,3	25, 100
FNT-3/4	3/4	1.030	26,1	1.050	26,7	0.820	20,8	0.840	21,3	25, 100
FNT-1	1	1.290	32,8	1.315	33,4	1.041	26,4	1.066	27,1	25, 100
FNT-1-1/4	1-1/4	1.630	41,4	1.660	42,2	1.380	35,1	1.410	35,8	25, 100
FNT-1-1/2	1-1/2	1.865	47,4	1.900	48,3	1.575	40,0	1.600	40,6	25, 50
FNT-2	2	2.340	59,4	2.375	60,3	2.020	51,3	2.045	51,9	25, 50



Toll Free: 1-800-52 ALPHA • Telephone: 908-925-8000 • Fax: 908-925-6923  
Europe/UK Telephone: +44 (0) 1932 772422 • Europe/UK Fax: +44 (0) 1932 772433

Web Site: [www.alphawire.com](http://www.alphawire.com)  
Email: [info@alphawire.com](mailto:info@alphawire.com)