


Product Details for 031 -0059 -0001



031 -0059 -0001

Tyco Part Number: 1466289 -1

[Active](#)

SMB RF Connectors

[RoHS Compliant](#) (Statement of Compliance)

Product Highlights:

- ? Connector
- ? Jack
- ? Miniature
- ? Terminate To Printed Circuit Board
- ? Coupler Style = Threaded

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [PRINTED CIRCUIT RECEPTACLE S -50 SERIES](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Gender](#) = Jack
- ? Connector Series = Miniature
- ? [Grade](#) = Commercial
- ? Safety Wire Holes = Without
- ? [PCB Mount Angle](#) = Vertical
- ? Board Standoff = Without
- ? Thread Size = 4.83 [.190] -32 UNF -2A
- ? PCB Mount Style = Thru Hole
- ? Body Material = Brass
- ? Dielectric Material = TEFLON

Mechanical Attachment:

- ? [Panel Attachment](#) = Without

Electrical Characteristics:

- ? [Connector Impedance \(?\)](#) = 50
- ? Environmental Seal = Without
- ? Solderless = No

Body Related Features:

- ? Coupler Style = Threaded
- ? [Pin Protection](#) = Without
- ? Solder Lug = Without
- ? [Body Plating](#) = Silver
- ? Terminal Style = Straight Pin

Contact Related Features:

- ? [Center Contact Plating](#) = Gold
- ? Contacts = With

Configuration Related Features:

- ? Terminal Length (mm [in]) = 3.94 [0.155]

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board

Other:

- ? Brand = Microdot