



CBB0250 Product Details

[Share](#) | [Print](#) | [Email](#)


CBB0250

TE Internal Number: 1-1437398-4

Obsolete

[Contact Product Information Center](#)

NEMA Terminal Blocks

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- CBB Series Block Series
- NEMA Product Line
- Block Type = Circuit Breaker
- Contact Configuration = Strap Clamp
- In-Line Circuit Protection Application

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Line Drawing](#)
- [Typical Assembly View](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Block Series](#) = CBB Series
- [Product Line](#) = NEMA
- [Block Type](#) = Circuit Breaker
- [Screw Size](#) = 8-32 Pan Head W/Clamp

Electrical Characteristics:

- [Voltage Rating \(VAC\)](#) = 250
- [Amperes \(A\)](#) = 2.5

Body Features:

- [Mount Style](#) = Channel Mount (Dovetail Base)
- [Wire Range \(Solid and Stranded\)\[MCM\] \(AWG\)](#) = 18-12
- [Blown Fuse Indicator](#) = Without
- [Blown Fuse Indicator Type](#) = None
- [Wire Strip Length \(mm \[in\]\)](#) = 12.70 [0.500]

Contact Features:

- [Contact Configuration](#) = Strap Clamp

Housing Features:

- [Housing Material](#) = Nylon

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Conditions for Usage:

- [Temperature, Max. \(°C\)](#) = 125

Operation/Application:

- [Application](#) = In-Line Circuit Protection

Other:

- [Brand](#) = Buchanan

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference Products](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

