



## General Information

<b>Kit Part Number:</b>	<a href="#">1-2110843-1</a>
<b>Description:</b>	Single, Double, 3 and 4 Pole, Double Throw, Printed Circuit Board and Wire Lug Terminals with Boot Seals Kit
<b>Application:</b>	Industrial, Instrumentation and Controls, Medical Equipment, Military/Aerospace, Telecommunications
<b>Family:</b>	Toggle
<b>TE Brand:</b>	ALCOSWITCH Products
<b>Solution:</b>	Circuit Control
<b>Product Type:</b>	Toggle Switch
<b>Number of Pieces:</b>	12
<b>RoHS:</b>	Yes

## Specifications

<b>Configuration:</b>	DPST - Double Pole Single Throw, SPST - Single Pole Single Throw, 3PDT - 3 Pole Double Throw, 4PDT - 4 Pole Double Throw
<b>Current Rating:</b>	3A, 6A
<b>Function:</b>	on / on, on / (on), (on) / off / (on) momentary, on / off / on
<b>Terminal Style:</b>	Wire Lug Terminals, Printed Circuit Board Terminals
<b>Tool Included:</b>	No
<b>Voltage Rating:</b>	125V, 250V

## Product Highlights

MT GREEN Series Epoxy Sealed Toggles are available in (14) Function Types, (10) Toggle & Bushing Styles, and (4) Termination Types. Break-Before-Make contacts rated at 6 Amps at 125 Volts AC and 3 Amps at 250 Volts AC with an operating temperature of -30°C to +85°C and wave solder capability to 265°C.

### Features and Benefits

- Wire Lug/Pin Terminals
- Right Angle and Vertical Right Angle
- Splash Proof Toggle Actuator
- Epoxy Sealed Terminals
- Actuator Guards
- Decorative Hardware
- Silicone Boot Seals Available

### Applications

- Telecommunications
- Instrumentation
- Medical Equipment



**Bill of Materials**

Part No.	Qty In Kit	Description	Datasheet	P/N Details	Search Distributors Inventory
<a href="#">1-1437558-0</a>	1	6A-125VAC; 3A-250VAC, 0.410" Long Round Toggle 1/4-40 Bushin...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">4-1437558-5</a>	1	6A-125VAC; 3A-250VAC, 0.410" Long Round Toggle 1/4-40 Bushin...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">2-1437558-8</a>	1	6A-125VAC; 3A-250VAC, 0.410" Long Round Toggle 1/4-40 Bushin...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">6-1437558-6</a>	1	6A-125VAC; 3A-250VAC, 0.600" Long Round Toggle w/Plastic Tip...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">7-1437558-1</a>	1	6A-125VAC; 3A-250VAC, 0.410" Long Round Toggle 1/4-40 Bushin...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">8-1437558-4</a>	1	6A-125VAC; 3A-250VAC, 0.485" Long Flat Toggle 1/4-40 Bushing...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">1-1437559-8</a>	1	6A-125VAC; 3A-250VAC, 0.452" Long Large Diameter Round Toggl...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">3-1437559-4</a>	1	6A-125VAC; 3A-250VAC, Locking Toggle 1/4-40 Bushing, SPDT-ON...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">4-1437559-9</a>	1	6A-125VAC; 3A-250VAC, 0.270" Long Round Toggle 1/4-40 Bushin...	<a href="#">Datasheet</a>	<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">1825619-1</a>	1	Half Boot Seal Black, 1/4-40 UNS 2-B Threaded Nut		<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">1825600-2</a>	1	Half Boot Seal Black, 15/32-32 UNS 2-B Threaded Nut		<a href="#">Details</a>	<a href="#">Search</a>
<a href="#">1825612-3</a>	1	Full Boot Seal Black, 1/4-40 UNS 2-B Threaded Nut		<a href="#">Details</a>	<a href="#">Search</a>

**Recommended Tool**

Part No.	Included in Kit
----------	-----------------







Kit Part No. **1-2110843-1**

## ALCOSWITCH MT Green Series Switch Kit

Single, Double, 3 and 4 Pole, Double Throw, Printed Circuit Board and Wire Lug Terminals

- Splash Proof Toggle Actuator
- Epoxy Sealed Terminals
- 6 Amps, 125 Volts AC; 3 Amps, 250 Volts AC
- 5 Toggle Lever Styles
- 3 Boot Seal types

Additional kits available at: [www.prdckts.com](http://www.prdckts.com)

ALCOSWITCH MT Connectivity, TE Connectivity, Teq and TTE Teq are trademarks of the TE Connectivity Ltd family of companies.  
©2012 TE. Failure to follow all instructions, including using only approved TE tools, may affect performance and safety. Use of non-approved tools and/or materials may void the warranty and may cause or contribute to improper use. Please refer to the instructions for additional safety and handling information.

**12**  
pieces



Product from TE Connectivity, Inc. designed and manufactured by Waldom Electronics.