


Product Details for 1 -770996 -5



1 -770996 -5

[Active](#)

MTA, CST -100 II, MT -6 and SL Connectors and Headers

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? SL-156 Housings
- ? Number of Positions = 13
- ? Mating Type = Receptacle
- ? Wire -to -Board Application
- ? 3.96 mm Contact Centerline Spacing

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [HOUSING WITHOUT LOCKINGRAMP AND WITH POLARIZINGTABS,...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? [SL 156 Contacts and Housings](#) (PDF, English)
- ? [MTA 156 Ribbon Cable Connector Assemblies \(English A...](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Additional Product Images:

- ? [Product Photo](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = SL -156 Housings
- ? [Number of Positions](#) = 13
- ? [Mating Type](#) = Receptacle
- ? [Wire Termination Type](#) = Crimp
- ? [Mating Polarization](#) = With
- ? Mating Connector Lock = Without
- ? [Four Points of Contact](#) = Without
- ? [Shrouded](#) = No
- ? [Mounting Ears](#) = Without
- ? Mating Polarization Method = Polarizing Tab

Mechanical Attachment:

- ? [Panel Attachment](#) = Without

Body Related Features:

- ? Cable Exit Angle = 180°

Contact Related Features:

- ? [Contact Centerline Spacing \(mm \[in\]\)](#) = 3.96 [0.156]

Housing Related Features:

- ? Housing Color = Natural
- ? Housing Flammability Rating = UL 94V -0
- ? Housing Material = Nylon

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- ? [Application](#) = Wire -to -Board

Packaging Related Features:

- ? Packaging Quantity = 500

Other:

- ? Brand = AMP