

Product Details for 1057289 - 1

No Image Available

1057289 - 1

 [Active](#)

N Series RF Connectors

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? Connector
- ? Jack Receptacle
- ? Terminate To Printed Circuit Board
- ? Body Style = Straight
- ? Commercial Grade

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [OSN 4 HOLE FLANGE MOUNT JACK RECEPTACLE](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? Gender = Jack Receptacle
- ? [Body Style](#) = Straight
- ? [Grade](#) = Commercial
- ? Lightning/EMP Protection = None
- ? [Dielectric Material](#) = TFE Fluorocarbon
- ? Weatherproof = No
- ? Body Material = Stainless Steel
- ? Terminal Type = Straight

Mechanical Attachment:

- ? [Panel Attachment](#) = With
- ? Panel Attachment Method = Square Flange
- ? [Panel Attachment Style](#) = Front Mount

Electrical Characteristics:

- ? Frequency = DC to 11 GHz
- ? Connector Impedance (?) = 50
- ? Insulation Resistance (M?) = 5,000

Body Related Features:

- ? [Body Plating](#) = Passivated

Contact Related Features:

- ? [Center Contact Plating](#) = Gold over Nickel
- ? Center Contact Material = Beryllium Copper

Housing Related Features:

- ? Captured Center Contact = Without

Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C, Reflow solder capable to 245°C, Reflow solder capable to 260°C, Pin -in -Paste capable to 245°C, Pin in -Paste capable to 260°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? Terminate To = Printed Circuit Board

Other:

- ? Brand = AMP