

1 - 87633 - 2 Product Details

No Image Available

1 - 87633 - 2

 [Active](#)

.156 Inch AMPMODU .031 X .062 Mod I

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? Header
- ? Vertical Mount Angle
- ? Gold (15) over Nickel (50) Contact Mating Area Plating
- ? Keyed
- ? Number of Positions = 12

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Header
- ? Mount Angle = Vertical
- ? [Keyed](#) = Yes
- ? [Number of Positions](#) = 12

Mechanical Attachment:

- ? [Mating Post Length \(mm \[in\]\)](#) = 10.29 [0.405]

Termination Related Features:

- ? Termination End Plating = Gold Flash over Nickel (50)

Body Related Features:

- ? Number of Rows = Single
- ? Centerline (mm [in]) = 3.96 [0.156]
- ? Number of Keys = 6

Contact Related Features:

- ? Contact Mating Area Plating = Gold (15) over Nickel (50)
- ? Contact Material = Brass

Housing Related Features:

- ? Housing Material = Polyester (PBT)
- ? Housing Color = Black
- ? Housing Flammability Rating = UL 94V -0

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? Terminate To = Printed Circuit Board

Other:

- ? Brand = AMP