


1-917360-0 Product Details

[Share](#) | [Print](#) | [Email](#)


1-917360-0

TE Internal Number: 1-917360-0
✔ Active

[View 3D PDF](#)

1.0mm, 1.25mm and 2.0mm Centerline Self-Aligning Connectors

✔ Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- 1.25 mm Centerline
- Connector Style = Receptacle
- Connector Design = Self Aligning (Alignment Free)
- 10 Positions
- Height = 5.40 mm

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) |
 [Request Sample](#) |
 [Find Similar Products](#) |
 [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [BLISTER TRAY PACKING 1.25 A-F CONN. REC ASSY \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Crimping Multi-Interlock Connector Contacts \(PDF, Japanese\)](#)

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version C\)](#)
- [3D Model \(IGES, Version C\)](#)
- [3D Model \(STEP, Version C\)](#)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [PCB Layout](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Connector Design = Self Aligning (Alignment Free)
- PCB Mount Style = Through Hole

Termination Features:

- Termination Post Length (mm [in]) = 3.20 [0.126]

Dimensions:

- Height (mm [in]) = 5.40 [0.213]

Contact Features:

- Contact Base Material = Phosphor Bronze
- Contact Plating, Mating Area, Material = Tin

Housing Features:

- Centerline (mm [in]) = 1.25 [0.049]
- Connector Style = Receptacle
- Housing Material = Nylon 6/6 GF

Configuration Features:

- Number of Positions = 10

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Packaging Features:

- Packaging Method = Tray
- Packaging Quantity = 264

Other:

- Brand = AMP

