

Catalog

- ▶ [Home](#)
- ▶ [Part Number Search](#)
- ▶ [Document Search](#)
- ▶ [CAD Model Search](#)
- ▶ [Text Search](#)
- ▶ [Alternate/Lead Free Part Search](#)
- ▶ [Multiple Part Comparison](#)
- ▶ [Alphabetical Search](#)
- ▶ [Brand Search](#)
- ▶ [Industry Product Search](#)
- ▶ [Product Type Search](#)
- ▶ [Product Family Search](#)
- ▶ [Competitor Cross Reference](#)
- ▶ [Lead Free Solutions](#)
- ▶ [Tool Search](#)
- ▶ [Help/Glossary](#)

AMPMODU**↳ .079, .100, .125, & .156 Centerline Crimp-Snap Housings**
AMP 1-925370-0  [Active](#) [Not Reviewed for ELV/RoHS Compliance](#)
**(Tyco Electronics P/N:
1-925370-0)**
[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information		
General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ▶ General Info ▶ Sales Info ▶ Assembly Subcontractors 	<ul style="list-style-type: none"> ▶ Pricing ▶ Product Availability 	<ul style="list-style-type: none"> ▶ Tooling

Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	Not reviewed for compliance
Lead Free Solder Process:	Not reviewed for lead free solder process
No. of Positions:	20
No. of Rows:	Dual
Housing Configuration:	Both Ends Closed
Centerline, Matrix (mm [in]):	2.54 x 2.54 [.100 x .100]
Contact Type:	Mod IV, Mod V
Mating Polarization:	No
Mating Connector Lock:	Without
Strain Relief:	With
Keyed:	No
Housing Material:	Nylon

Other Properties:

Housing Flammability Rating:	UL 94-HB
Housing Color:	Green
Packaging Quantity:	25

[Copyright](#) and [Privacy Statement](#)

Visit [Tyco International, Ltd.](#)

[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)