


Product Details for 1064523 - 1



1064523 - 1

[Active](#)

RF Coax Cable Assemblies

[RoHS Compliant](#) (Statement of Compliance)

Product Highlights:

- ? 2 Connectorized Ends
- ? SSMT Application
- ? Connector Type = SSMT Right Angle Jack
- ? Assembly Length = 75.00 mm

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [SSMT RIGHT ANGLE JACK TO JACK CABLE ASSEMBLY](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Connector Type](#) = SSMT Right Angle Jack
- ? Dielectric Material = PTFE Fluorocarbon
- ? Shield Material = Copper Wire

Electrical Characteristics:

- ? Frequency = DC to 6 GHz
- ? Connector Impedance (?) = 50
- ? Voltage (VAC) = 250
- ? Insulation Resistance (M?) = 1,000

Body Related Features:

- ? [Number of Connectorized Ends](#) = 2
- ? [Assembly Length \(mm \[in\]\)](#) = 75.00 [2.950]
- ? Conductor Material = Copper clad Steel
- ? Jacket Material = FEP Fluorocarbon
- ? Conductor Plating = Silver
- ? Shield Plating = Silver

Contact Related Features:

- ? Contact Material = Beryllium Copper
- ? Contact Mating Area Plating = Gold over Nickel

Configuration Related Features:

- ? Conductor (Wire) Size = 30 AWG

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- ? Application = SSMT

Other:

- ? Brand = AMP