


Product Details for 111035 - 3



111035 - 3

[Active](#)

Ribbon Cable Connectors (AMP - LATCH)

[Not ELV or RoHS Compliant](#) [\(Find RoHS Compliant Alternates\)](#)

Product Highlights:

- ? Connector Type = Paddleboard
- ? Number of Positions = 20
- ? Without Mating Polarization
- ? Terminate To Printed Circuit Board
- ? Without Mounting Ears

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [KIT, AMP -LATCH PADDLEBOARD PREASSEMBLED, .100 LONG ...](#)
(PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [3D Model](#) (STEP, Version G)
- ? [3D Model](#) (IGES, Version G)
- ? [2D Drawing](#) (DXF, Version G)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Connector Type = Paddleboard
- ? [Number of Positions](#) = 20
- ? [Mating Polarization](#) = Without
- ? [Mounting Ears](#) = Without
- ? Special PCB Retention = Without
- ? Mating Connector Lock = Without
- ? Strain Relief = Without
- ? With Cover Preassembled = Yes
- ? PCB Thickness (mm [in]) = 1.60 [0.063]

Contact Related Features:

- ? [Contact Mating Area Plating](#) = Tin
- ? [Contact Termination Area Plating](#) = Tin
- ? Contact Material = Phosphor Bronze

Housing Related Features:

- ? [Housing Color](#) = Black
- ? Housing Material = Thermoplastic Polyester
- ? Housing Flammability Rating = UL 94V -0

Configuration Related Features:

- ? Cable Stop = Without

Industry Standards:

- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board

Other:

- ? Brand = AMP