

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



Always EU RoHS/ELV Compliant (Statement of Compliance)

- ? Connector
- ? Product Series = 90
- ? Density = High
- ? Terminate To Wire
- ? Number of Positions = 78

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

[AMPLIMITE RECEPTACLE ASSY,SIZE 1 THRU 6 SERIES 90 WI...](#)
(PDF, English)

? None Available

? None Available

? None Available

? None Available

- ? 2D Drawing (DXF, Version B)
- ? 3D Model (IGES, Version B)
- ? 3D Model (STEP, Version B)

? Product Line Information

? Insert Arrangement

? Tooling

List all Documents

Product Type Features:

- ? Product Type = Connector
- ? Product Series = 90
- ? Number of Positions = 78
- ? Gender = Receptacle
- ? Shell Size = 5
- ? Shell Material = Steel
- ? Wire Termination Type = Crimp
- ? Mounting Hole Diameter (mm [in]) = 3.05
[.120]
- ? Comment = Size 22 sockets supplied with receptacles are loose piece.; "F" is stamped on connectors following M24308 part number as required. "F" designates cadmium shell plating.

- ? Blindmate = No
- ? Non - Magnetic = No
- ? Sockets = Without
- ? Rear Grommet = No
- ? Power/Signal/Coax Combination = No
- ? Shell Plating = Zinc
- ? Mount Style = Mounting Holes
- ? Retention Clip Material = Stainless Steel

? Contact Size = 22

? Contact Style = Crimp Snap -in

? Density = High

- ? Government/Industry Qualification = Yes
- ? Government/Industry Part Number = M24308/2290
- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant
- ? NASA Qualification = No

? Terminate To = Wire

? Brand = AMP