



**CONNECTORS**

HEADERS & RECEPTACLES



✓ Active

TE CONNECTIVITY (TE)

## CT P/HDR BOX V 10P BLUE

AMP CT | AMP CT

3-292132-0

TE Internal Number: 3-292132-0

EU RoHS Compliant

EU ELV Compliant

Connector System Wire-to-Board

Number of Positions 10

Centerline (Pitch) (mm) 2

PCB Mounting Orientation Vertical

PCB Mounting Style Through Hole

[↓ PRODUCT DRAWING](#)  
English

[↓ 3D PDF](#)

### DOCUMENTATION

Product Drawings

#### **POST HEADER ASS'Y (BOX-V DIP) (AMP CT CONNECTOR 2mm PITCH)**

PDF

English

CAD Files

#### **3D PDF**

PDF

3D

#### **Customer View Model**

2D\_DXF.ZIP

English

## Customer View Model

3D\_IGS.ZIP

English

## Customer View Model

3D\_STP.ZIP

English

---

Product Specifications

Product Specification

### AMP COMMON TERMINATION (CT), CONNECTOR, 2mm PITCH, M/T TYPE, LEAD FREE VERSION

TIF

Japanese

### AMP COMMON TERMINATION (CT), CONNECTOR, 2mm PITCH, M/T TYPE, LEAD FREE VERSION

PDF

Japanese

### AMP COMMON TERMINATION (CT), CONNECTOR, 2mm PTICH, M/T TYPE, LEAD FREE VERSION

PDF

English

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

### Product Type Features

**Connector System** Wire-to-Board

**PCB Mounting Orientation** Vertical

**Header Type** Shrouded

**Sealable** No

**Product Type** Connector

**Connector Type** Header

**Shape** Rectangular

**Connector Style** Header

**Strain Relief** Without

**Wire/Cable Type** Discrete Wire

---

### Configuration Features

**Number of Positions** 10

**Number of Rows** 1

**Tail Orientation** Inline

**Backwall/Post Interruptions** Without

---

### Electrical Characteristics

**Operating Voltage (VAC)** 125

**Operating Voltage (VDC)** 125

---

### Contact Features

**Contact Shape** Rounded  
**Contact Mating Area Plating Material** Tin  
**Contact Mating Area Plating Thickness** 1 µm [ 39.37 µin ]  
**Contact Current Rating (Max) (A)** 4  
**Contact Base Material** Brass  
**Contact Termination Area Plating Material** Tin  
**Contact Termination Area Plating Thickness** 1 µm [ 39.37 µin ]  
**Contact Transmits (Typical)** Signal (Data)  
**Contact Design** Round Post  
**Tail Plating Material** Tin  
**Contact Type** Pin

---

#### Termination Features

**Termination Method to PC Board** Through Hole - Solder

---

#### Mechanical Attachment

**PCB Mounting Style** Through Hole  
**PCB Mount Alignment** Without  
**PCB Mount Alignment Type** Kinked Legs  
**Mating Retention** Without  
**PCB Mount Retention** With  
**PCB Mount Retention Type** Kinked Legs  
**Mating Alignment** With  
**Mating Retention Type** Polarized Lock  
**Mating Alignment Type** Polarization  
**Contact Retention** Without

---

#### Housing Features

**Centerline (Pitch) (mm)** 2  
**Housing Material** 66 Nylon  
**Housing Color** Blue

---

#### Dimensions

**Height** 6.8 mm [ .267 in ]  
**Tail Length** 3.2 mm [ .126 in ]  
**Width** 5.8 mm [ .228 in ]  
**PCB Thickness (Recommended)** .8 mm [ .031 – .063 in ]  
**Length** 21.8 mm [ .8583 in ]  
**Wire/Cable Size (AWG)** 28 – 22  
**Mating Post Length** 4.2 mm [ .165 in ]

---

#### Usage Conditions

**Operating Temperature Range** -40 – 221 °C [ -40 – 105 °F ]

---

#### Operation/Application

**Pick and Place Cover** Internal

---

#### Industry Standards

**Agency/Standard** UL 94V-0, UL  
**CSA File Number** LR 7189  
**UL Flammability Rating** UL 94V-0  
**Agency/Standard Number** CSA, UL  
**UL File Number** E28476

---

Packaging Features

**Packaging Reel Diameter** 500  
**Packaging Method** Bag/Box  
**Packaging Quantity** 500

---

**PRODUCT COMPLIANCE**



Statement of Compliance

**Statement of Compliance**

PDF

---