


174778 -1 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



174778 -1

✓ [Active](#)

Positive Lock Connectors

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Receptacle
- ? Tab Fit = 2.79 x 0.51 mm
- ? Line = Mark II
- ? Receptacle Style = Straight
- ? Wire Range = 0.50 -1.40² [20-16] mm [AWG]

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [View Housings \(5\)](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [110 SERIES POSITIVE LOCK REC. CONTACT](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [110 SERIES POSITIVE LOCK MARK -II CONNECTOR](#) (PDF, English)
- ? [JAPANESE](#) (PDF, English)

Application Specifications:

- ? [Crimping 110 Series, Positive Lock Contact](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)
- ? [Housings \(5\)](#)

[List all Documents](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Receptacle
- ? [Tab Fit \(mm \[in\]\)](#) = 2.79 x 0.51 [.110 x .020]
- ? [Receptacle Style](#) = Straight
- ? [Insulation Diameter \(mm \[in\]\)](#) = 2.10 -3.10 [.083 -.122]
- ? [Material](#) = Brass
- ? [Finish](#) = Pre -Tin
- ? [Keyed](#) = No

Body Related Features:

- ? [Wire Range \(mm \[AWG\]\)](#) = 0.50 -1.40² [20-16]
- ? [Position Keyed](#) = None

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? [Packaging Method](#) = Loose Piece

Other:

- ? [Line](#) = Mark II
- ? Brand = AMP