



[CONNECTORS](#)

CONNECTOR CONTACTS



✓ Active

TE CONNECTIVITY (TE)

CONTACT, SOCKET, AUDIO MICRO

[Audio Contacts](#) | [Audio Contacts](#)

207437-2

TE Internal Number: 207437-2

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

Contact Type Socket

Contact Mating Area Plating Material Tin

Operating Voltage (VAC) 250

Contact Size 16

Contact Classification Signal

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

CONTACT, SOCKET

PDF (TIFF AVAILABLE)

English

CAD Files

3D PDF

PDF

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Customer View Model

2D_DXF.ZIP

English

Product Specifications

Application Specification

Audio/Microphone Connectors

PDF

English

Product Environmental Compliance

TE Material Declaration

MD_207437-2_10202016935_dmtec

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector & Contact Terminates To Wire & Cable

Product Type Contact

Grade Commercial

Electrical Characteristics

Operating Voltage (VAC) 250

Test Current (A) 10

Contact Features

Contact Type Socket

Contact Mating Area Plating Material Tin

Contact Size 16

Contact Classification Signal

Contact Base Material Brass

Contact Current Rating (Max) (A) 10

Contact Diameter (mm) 1.93

Termination Features

Termination Method to Wire/Cable Crimp

Termination End Plating Material Tin

Dimensions

Wire/Cable Size .05 – .4 mm², 28 – 22 AWG

Accepts Wire Insulation Diameter Range .91 – 1.37 mm [.036 – .054 in]

Operation/Application

For Use With CPC Connectors

High Current No

Packaging Features

Packaging Method Strip

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
