




[+ TERMINALS & SPLICES](#)
[RINGS & SPADES](#)



✓ Active

TE CONNECTIVITY (TE)

TERMINAL, PG RECT 16-14 6

[PLASTI-GRIP](#) | [PLASTI-GRIP](#)

34898

TE Internal Number: 34898

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

Terminal Type Rectangular Tongue

Stud Diameter 3.68 mm [.145 in]

Tongue Thickness .79 mm [.031 in]

Wire Size (AWG) 16 – 14

Wire Size (mm²) 1.04 – 2.62

[↓ PRODUCT DRAWING](#)
English

DOCUMENTATION

Product Drawings

TERMINAL, RECTANGULAR TONGUE, PLASTI-GRIP, 16-14

PDF (TIFF AVAILABLE)

English

Product Specifications

Application Specification

PLASTI GRIP Terminals And Splices

PDF

English

Agency Approvals

UL Report

Plasti-Grip Terminals And Butt And Parallel Connectors

PDF

English

WIRE CONN, TERMINALS, BUTT AND PARALLEL CONNECTORS-PLASTI-GRIP, SOLISTRAND, STD B, DIAMOND GRIP, PIDG AND AMPOWER REPORT

PDF

English

CSA Certificate

PLASTI-GRIP INSULATED BUTT SPLICES, TERMNAL SPLICES AND TERMINALS REPORT

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Sealable No

Barrel Type Closed Barrel

Wire/Cable Type Regular Wire

Insulated Yes

Insulated Wire Support Yes

Support Style Insulation Support

Stud Size 6, M3.5

Barrel Style Standard

Shape Code RING-055

Wire/Cable Composition Solid or Stranded

Configuration Features

Number of Holes 1

Terminal Angle Straight

Electrical Characteristics

Voltage (Max) (V) 600

Body Features

Plating Material Copper, Tin

Weight per Piece (g) .183

Plating Thickness 2.54 μm [100 μin]

Insulation Material Vinyl

Inspection Slot No

Contact Features

Terminal Type Rectangular Tongue

Terminal Orientation Straight

Dimensions

Stud Diameter 3.68 mm [.145 in]
Tongue Thickness .79 mm [.031 in]
Wire Size (AWG) 16 – 14
Wire Size (mm²) 1.04 – 2.62
Wire Insulation Diameter (Max) 3.68 mm [.145 in]
Wire Insulation Diameter (mm) 2.67 – 3.68
Wire Size (CMA) 2050 – 5180
Barrel Inside Diameter 3.84 mm [.151 in]
Material Thickness .79 mm [.031 in]
Overall Length 22.05 mm [.87 in]
Barrel Inside Diameter (Min) (in) .151

Usage Conditions

Operating Temperature Range (°C) 105

Operation/Application

Heavy Duty No

Industry Standards

Government Qualified No

Packaging Features

Packaging Method Loose Piece
Packaging Quantity 1000

Other

Barrel Color Blue

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
