


Product Details for 322 -HCS6P2 - 100



Discrete Sockets

[RoHS Compliant](#) (Statement of Compliance)

Product Highlights:

- ? Socket
- ? Mating Pin Dia. Range = .51 - .76 mm
- ? Socket Length = 3.56 mm
- ? Gold Contact Spring Plating
- ? Production Application

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

322 -HCS6P2 - 100

Tyco Part Number: 4 - 1437514 - 3

[Active](#)

Documentation & Additional Information

Product Drawings:

? None Available

Catalog Pages/Data Sheets:

? None Available

Product Specifications:

? [AUGAT* HOLTITE* Sockets](#) (PDF, English)

Application Specifications:

? [AUGAT HOLTITE Sockets](#) (PDF, English)

Instruction Sheets:

? None Available

CAD Files:

? None Available

Additional Information:

? [Product Line Information](#)

Additional Product Images:

? [Product Photo](#)

Related Products:

? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Socket
- ? [Socket Length \(mm \[in\]\)](#) = 3.56 [0.140]
- ? [Sealant](#) = Without
- ? Proprietary Name = HOLTITE
- ? Recommended Hole Size (mm [in]) = 1.61 [0.0635]

Body Related Features:

- ? [Mating Pin Dia. Range \(mm \[in\]\)](#) = 0.51 - 0.76 [0.020 - 0.030]
- ? Spring Material = Beryllium Copper

Contact Related Features:

- ? [Contact Spring Plating](#) = Gold
- ? [Contact Material](#) = Beryllium Copper

Configuration Related Features:

- ? [Insertion Method](#) = Hand/Semi - Automatic/Automatic

Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- ? Application = Production

Packaging Related Features:

- ? Packaging Method = Reel

Other:

- ? Brand = AMP