


**Product Details for 2 -329944 -3**



**2 -329944 -3**

[Active](#)

**Twin Threaded RF Connectors**

[Not ELV or RoHS Compliant](#) (Find RoHS Compliant Alternates)

**Product Highlights:**

- ? Connector
- ? Plug
- ? Coaxial Cable Type (RG/U or Mfg.) = Belden 8451, Belden 8641, Belden 8761
- ? Terminate To Coaxial Cable
- ? Without Panel Attachment

[View all Features](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling Product Feature Selector](#)
- [Contact Us About This Product](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [TWIN THREADED PLUG](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- ? None Available

**Product Specifications:**

- ? None Available

**Application Specifications:**

- ? None Available

**Instruction Sheets:**

- ? [AMP\\* THEADED -TYPE TWIN COAXICON\\* CONNECTORS](#) (PDF, English)

**CAD Files:**

- ? None Available

**Additional Information:**

- ? [Product Line Information](#)

**Related Products:**

- ? [Tooling](#)

[List all Documents](#)

**Product Features** (Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? Product Type = Connector
- ? [Gender](#) = Plug
- ? Crimp Type = Single
- ? Dielectric Material = Polypropylene

**Mechanical Attachment:**

- ? Panel Attachment = Without

**Termination Related Features:**

- ? Coaxial Cable Termination Type = Crimp

**Body Related Features:**

- ? [Body Plating](#) = Silver

**Contact Related Features:**

- ? Center Contact Plating = Gold

**Configuration Related Features:**

- ? [Coaxial Cable Type \(RG/U or Mfg.\)](#) = Belden 8451, Belden 8641, Belden 8761

**Industry Standards:**

- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process

**Conditions for Usage:**

- ? [Terminate To](#) = Coaxial Cable

**Other:**

- ? Brand = AMP