


**Product Details for 535068 - 4**



**535068 - 4**

[Active](#)

**Eurocard Type C**

[RoHS/Not ELV Compliant](#) (Find RoHS Compliant Alternates/Compliance Statement)

**Product Highlights:**

- ? Type C Connectors
- ? Receptacle
- ? Number of Positions = 32
- ? Rows Loaded = A
- ? Rows Loaded = C

[View all Features](#)

**Quick Links**

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

**Documentation & Additional Information**

**Product Drawings:**

- ? [ASSEMBLY, RECEPTACLE, EUROCARD, TOOLLESS PRESSFIT, 4...](#) (PDF, English)

**Catalog Pages/Data Sheets:**

- ? None Available

**Product Specifications:**

- ? None Available

**Application Specifications:**

- ? [Eurocard Connectors Types B,C,M,Q,R, & Enhanced Typ...](#) (PDF, English)

**Instruction Sheets:**

- ? None Available

**CAD Files:** ([CAD Format & Compression Information](#))

- ? [3D Model](#) (STEP, Version L)
- ? [3D Model](#) (IGES, Version L)
- ? [2D Drawing](#) (DXF, Version L)

[List all Documents](#)

**Additional Information:**

- ? [Product Line Information](#)

**Related Products:**

- ? [Tooling](#)

**Product Features** (Please use the Product Drawing for all design activity)

**Product Type Features:**

- ? [Product Type](#) = Type C Connectors
- ? [Gender](#) = Receptacle
- ? [Number of Positions](#) = 32
- ? [Special PCB Retention](#) = With
- ? [Special PCB Retention Method](#) = Compliant Pin
- ? [PCB Mount Angle](#) = Vertical
- ? [PCB Thickness \(Minimum\) \(mm \[in\]\)](#) = 1.57 [0.062]
- ? [Post Type](#) = Compliant Post
- ? [Size](#) = Half
- ? [Make First / Break Last](#) = No
- ? [DIN Level](#) = II
- ? [Mounting Ears](#) = With
- ? Toolless (Flat Rock) = Yes
- ? Color = Gray
- ? Comment = Contact Finish: DIN 41612 Class 2 In Contact Area. Tin-Lead On Solder Tails.

**Termination Related Features:**

- ? [Termination Post Length \(mm \[in\]\)](#) = 4.83 [0.190]

**Body Related Features:**

- ? [Rows Loaded](#) = A, C
- ? [Contact Cross Section \(mm \[in\]\)](#) = 0.30 x 0.61 [.012 x .024]

**Contact Related Features:**

- ? Contact Material = Phosphor Bronze
- ? Contact Termination Area Plating = DIN41612 Class 2

**Housing Related Features:**

- ? Housing Material = Polyester
- ? Housing Flammability Rating = UL 94V -0

**Industry Standards:**

- ? [RoHS/ELV Compliance](#) = RoHS/Not ELV Compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? [Flux - Tight Coating](#) = Without
- ? RoHS/ELV Compliance History = Always was RoHS not ELV compliant

**Conditions for Usage:**

- ? [Terminate To](#) = Printed Circuit Board
- ? [High Temperature Housing](#) = No

**Other:**

- ? Brand = AMP