


735222 -1 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



735222 -1

[Active](#)

Multiple Circuit Housings with Tabs & Receptacles Including FASTIN -FASTON

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Receptacle
- ? Tab Fit = 6.35 x 0.81 mm
- ? Wire Range = 1.00 -2.50² [17-13.5] mm [AWG]
- ? Insulation Diameter = 3.00 -4.29 [.118 -.169] mm [in]
- ? Receptacle Style = Straight

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [TERMINAL, 6,3 SERIES FATIN FATON RCPT.](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Receptacle
- ? [Tab Fit \(mm \[in\]\)](#) = 6.35 x 0.81 [.250 x .032]
- ? [Insulation Diameter \(mm \[in\]\)](#) = 3.00 -4.29 [.118 -.169]
- ? [Receptacle Style](#) = Straight
- ? [Wire/Cable Type](#) = Regular Wire
- ? [Finish](#) = None
- ? [Material](#) = Brass
- ? [Insertion Force](#) = Normal
- ? [Insulation Support](#) = With
- ? [Crimp Type](#) = "F"
- ? FASTON = Yes

Body Related Features:

- ? [Wire Range \(mm \[AWG\]\)](#) = 1.00 -2.50² [17-13.5]

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? [Packaging Method](#) = Strip

Other:

- ? Line = FASTIN -FASTON .250
- ? Brand = AMP