


1544118-1 Product Details

[Share](#) | [Print](#) | [Email](#)


1544118-1

TE Internal Number: 1544118-1
✔ Active

[View 3D PDF](#)

Leadframes

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Leadframe
- Clip Style = Single-In-Line (SIL)
- Clip Type = Y1
- 2.50 mm Centerline
- Through Hole Contact Termination Type

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [LEAD FRAME SIL \(PDF, English\)](#)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version H\)](#)
- [3D Model \(IGES, Version H\)](#)
- [3D Model \(STEP, Version H\)](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Leadframe
- Clip Style = Single-In-Line (SIL)

Mechanical Attachment:

- Holddown Feature = Without

Electrical Characteristics:

- Clip Type = Y1
- Solder Inlay = Without

Termination Features:

- Contact Termination Type = Through Hole

Dimensions:

- Frame Width (mm [in]) = 28.00 [1.102]
- Frame Thickness (mm [in]) = 0.25 [0.010]
- Circuit Thickness (mm [in]) = 0.63 [0.025]
- Clip Length (mm [in]) = 1.70 [0.067]

Body Features:

- Pin Length (mm [in]) = 19.70 [0.775]

Contact Features:

- Contact Plating = Pre-Tinned
- Contact Base Material = Phosphor Bronze

Housing Features:

- Centerline (mm [in]) = 2.50 [0.098]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant


Packaging Features:

- Packaging Quantity = 40,000

Other:

- Brand = TE Connectivity

Corporate Information | Quick Links | Customer Support | Keep Me Informed

<p>Corporate Information</p> <ul style="list-style-type: none"> About TE Investors News Room Supplier Portal Careers Terms & Conditions Privacy Policy 	<p>Quick Links</p> <ul style="list-style-type: none"> Check Distributor Inventory Cross Reference Products Find Documents & Drawings Product Compliance Support Center Site Map 	<p>Customer Support</p> <ul style="list-style-type: none"> Email or Chat With Us Find a Phone Number Search Knowledge Base Manage Your Account 	<p>Keep Me Informed</p> <p>Receive TE News, Events & Technology Updates</p> <input type="text" value="Enter your email address"/> 
--	---	---	--

