

## 4-1734376-8 Product Details

 [Live Product Chat](#)


### 4-1734376-8

TE Internal Number: 4-1734376-8

 [Active](#)

### Universal Serial Bus (USB) Connectors

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Size = Standard
- B Series
- Receptacle
- Without Locking Feature
- 1 Ports

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

   

### Documentation & Additional Information

#### Product Drawings:

- [USB CONN. SERIES B, 4P, R/A, THRU HOLE, W/ BACK SHELL \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Size = Standard
- Gender = Receptacle
- Number of Ports = 1
- Orientation = Right Angle
- Number of Positions = 4

#### Mechanical Attachment:

- Mount Location = Top

#### Termination Related Features:

- Termination Method = Solder to PC Board
- Tail Length (mm [in]) = 2.91 [0.115]

#### Body Related Features:

- [Series](#) = B
- Locking Feature = Without
- LED = Without
- [Panel Ground](#) = Without
- PCB Retention Method = Kinked Leg
- Shell Plating = Bright Tin
- Assembly Process Feature = Without Pick and Place Cover
- Locating Post(s) = Without

#### Contact Related Features:

- Contact Termination Type = Through Hole
- [Contact Mating Area Plating Material](#) = Gold
- Contact Mating Area Plating Thickness = 30 Microinches

#### Housing Related Features:

- [Housing Color](#) = Natural

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- Terminate To = Printed Circuit Board

#### Packaging Related Features:

- [Packaging Method](#) = Tray

#### Other:

- Brand = AMP