


## 8-53424-2 Product Details

Have a Question?

Chat with a Product Information Specialist



8-53424-2

### Radiation Resistant/Pre-Insulated Terminals & Splices

[Not EU RoHS or ELV Compliant \(Find RoHS Compliant Alternates\)](#)

#### Product Highlights:

- Terminal
- Wire Range = 3.00-6.00<sup>2</sup> [12-10] mm [AWG]
- Wire Range = 5180 - 13100 CMA
- Body Style = PIDG
- Wire Insulation Diameter = 5.84 mm

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TE Internal Number: 8-53424-2

 Active

 [View 3D PDF](#)

[Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [TERMINAL, RING TONGUE, PVF2 , P.I.D.G. WIRE SIZE: 12...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: [\(CAD Format & Compression Information\)](#)

- [2D Drawing](#) (DXF, Version S1)
- [3D Model](#) (IGES, Version S1)
- [3D Model](#) (STEP, Version S1)

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Terminal
- [Body Style](#) = PIDG
- [Wire Insulation Diameter \(mm \[in\]\)](#) = 5.84 [0.230]
- [Stud Size](#) = 8 [M4]
- [Finish](#) = Tin-Lead
- Tongue Material Thickness (mm [in]) = 1.04 [0.041]
- Color Code = Yellow
- Body Material = Copper
- Insulation = Yes
- Comment = Brazed Body

#### Body Related Features:

- [Wire Range \(mm \[AWG\]\)](#) = 3.00-6.00<sup>2</sup> [12-10]
- [Wire Range \(CMA\)](#) = 5,180 - 13,100
- Insulation Sleeve Color = Natural
- Insulation Sleeve Material = PVF2
- Insulation Support Sleeve Material = Copper

#### Industry Standards:

- Government/Industry Qualification = No
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

#### Packaging Related Features:

- [Packaging Method](#) = Loose Piece
- Packaging Quantity = 50

#### Other:

- Brand = AMP

 BOOKMARK 

#### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)

#### Sign up for our eNewsletter

Enter your email address

#### Follow Us On:



Visit Us On:

