


Product Details for 5650712 - 1



5650712 - 1

[Active](#)

.050 Standard Edge and Press - Fit Connectors

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? 15 Dual Positions
- ? PCB Termination Type = Solder
- ? Mating Polarization Method = End Key
- ? Termination Post Length = 2.54 mm
- ? Daughter Board Thickness = 1.37 - 1.78 mm

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [CONNECTOR ASSEMBLY, END KEYED, 15 DUAL POSITION, .05...](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [Connector, Card Edge, .050 Centerline](#) (PDF, English)

Application Specifications:

- ? [Card Edge PC Board Connectors](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [3D Model](#) (STEP, Version A)
- ? [3D Model](#) (IGES, Version A)
- ? [2D Drawing](#) (DXF, Version A)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Number of Dual Positions](#) = 15
- ? [PCB Termination Type](#) = Solder
- ? [Mating Polarization Method](#) = End Key
- ? Bus Type = PS/2

Termination Related Features:

- ? [Termination Post Length \(mm \[in\]\)](#) = 2.54 [0.100]

Body Related Features:

- ? Centerline (mm [in]) = 1.27 [0.050]

Contact Related Features:

- ? Contact Material = Phosphor Bronze
- ? Contact Mating Area Plating = Gold (30)
- ? Contact Termination Area Plating = Tin
- ? Contact Underplating = Nickel (50)

Housing Related Features:

- ? Housing Material = High Temperature Thermoplastic
- ? Housing Color = Brown

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- ? [Daughter Board Thickness \(mm \[in\]\)](#) = 1.37 - 1.78 [0.054 - 0.070]
- ? Brand = AMP