


[English](#) [日本語](#)
**Electronics**
*a vital part of your world*

 Find  
Answers:

Tuesday, 18 October, 2005

**CATALOG**

 → [Cross Reference](#)
[Competitive Products](#)
[Military Spec P/Ns](#)
[Tyco Brand P/Ns](#)

 → [Part Number Search](#)

 → [Document Search](#)

 → [Product Type Search](#)

 → [Product Family Search](#)

 → [Alphabetical Search](#)

 → [RoHS/ELV Compliance &](#)
[Alternates](#)

 → [CAD Model Search](#)

 → [Brand Search](#)


 → [Tool Search](#)

 → [Multiple Part Comparison](#)

 → [Lead Free Solutions](#)

 → [Help/Glossary](#)
[Home](#)

 e-bulletin newsletter  
**SUBSCRIBE NOW!**  
 click here

**Terminals and Splices**
**↳ Ring and Spade Tongue Terminals**
**AMP** **60319-2**  [Active](#)
**Directive 2002/95/EC  
Compliant**
[RoHS Compliant](#)
**(Corporate P/N: 60319-2)**
[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

**Related Part Information**

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> <li>↳ <a href="#">General Info</a></li> <li>↳ <a href="#">Sales Info</a></li> <li>↳ <a href="#">Assembly Subcontractors</a></li> </ul>	<ul style="list-style-type: none"> <li>↳ <a href="#">Pricing</a></li> <li>↳ <a href="#">Product Availability</a></li> </ul>	<ul style="list-style-type: none"> <li>↳ <a href="#">Tooling</a></li> </ul>

**Photos & Line Drawings** - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)
**Searchable Features:**

<b>Brand:</b>	AMP
<b>Government/Industry Qualification:</b>	No
<b>RoHS/ELV Compliance:</b>	RoHS compliant, ELV compliant
<b>Lead Free Solder Processes:</b>	Not relevant for lead free process
<b>Terminal Shape:</b>	Ring Tongue
<b>Receptacle Style:</b>	Straight
<b>Body Style:</b>	AMPLIVAR
<b>Barrel Type:</b>	Open Barrel
<b>Wire/Cable Type:</b>	Magnet Wire

**Other Properties:**

<b>Stock Thickness (mm [in]):</b>	0.51 [0.020]
-----------------------------------	--------------

<b>Wire Range (mm [AWG]):</b>	0.574-0.912 [23-19]
<b>Insulation:</b>	No
<b>Insulation Support:</b>	Insulation Support
<b>Insulation Diameter (mm [in]):</b>	2.54-3.56 [.100-.140]
<b>Stud Size:</b>	10
<b>Stud Diameter (mm [in]):</b>	5.00 [0.197]
<b>Shape:</b>	RING-028
<b>Heavy Duty:</b>	No
<b>Packaging Method:</b>	Strip
<b>Material:</b>	Brass
<b>Finish:</b>	Tin

[Copyright](#) and [Privacy Statement](#)  
Visit [Tyco International Ltd.](#)

[ [Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#) ]