



## 1379731-1 Product Details

[Share](#) [Print](#) [Email](#)



1379731-1

TE Internal Number: 1379731-1

 Active

 [View 3D PDF](#)

### Micro-Power & Power Quadlok System

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Applies To Printed Circuit Board
- Connector
- Header
- Connector Style = Plug
- Termination Method to PC Board = Through Hole - Solder

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [18W MQS HEADER BENT LEFT WITH CRESSING PIN EMBASE 18...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- [Embase 18 Voies MQS Coudee](#) (PDF, French)

#### Application Specifications:

- None Available

#### Instruction Sheets:

- [Embase 18 Voies MQS Coudee Avec Pion de Bouterollage](#) (PDF, French)

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version B)
- [3D Model](#) (IGES, Version B)
- [3D Model](#) (STEP, Version B)

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Connector
- Connector Type = Header
- Termination Method to PC Board = Through Hole - Solder
- Sealed = No
- Mount Angle = 90°
- Material = PCT-GF30
- Keyed = Yes

#### Body Features:

- [Number of Positions](#) = 18
- [Centerline, Matrix \(mm \[in\]\)](#) = 2.54 x 2.54 [.100 x .100]
- Staggered Centerline = Without
- Mates with Centerline = 2.54 x 2.54 [.100 x .100]
- Key ID = 1

#### Contact Features:

- Contact Type = Tab
- Contact Style = MQS
- Number of MQS Contacts = 18
- [Contact Finish](#) = Tin

#### Housing Features:

- Connector Style = Plug
- Header Color = Black

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- Applies To = Printed Circuit Board

#### Packaging Features:

- [Packaging Method](#) = Tray

#### Other:

- GET 0.64 Connector System = No
- Brand = AMP

#### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

#### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

