


## 644518-4 Product Details

[Live Product Chat](#)



**644518-4**

TE Part Number: 644518-4

[Active](#)

[Add to Part List](#)

### MTA, CST-100 II, MT-6 and SL Connectors and Headers

Not EU RoHS or ELV Compliant ([Find RoHS Compliant Alternates](#))

#### Product Highlights:

- MTA-100 Connectors
- Number of Positions = 4
- Mating Type = Header
- Wire-to-Board Application
- 2.54 mm Contact Centerline Spacing

[View all Features](#) | [Find Similar Products](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

**NEW!**

### Documentation & Additional Information

#### Product Drawings:

- [MTA-100 HEADER ASSEMBLY, FRICTION LOCK, NOTCHED, .025 ...](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version F)
- [3D Model](#) (IGES, Version F)
- [3D Model](#) (STEP, Version F)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = MTA-100 Connectors
- [Number of Positions](#) = 4
- [Mating Type](#) = Header
- [PCB Mount Angle](#) = Vertical
- PCB Retention Feature = No
- [Mating Polarization](#) = With
- [Mating Connector Lock](#) = With
- [Four Points of Contact](#) = Without
- [Shrouded](#) = No
- [Mounting Ears](#) = Without
- Mating Connector Lock Type = Friction Lock
- PCB Thickness (mm [in]) = 1.60 [0.063]
- Post Size (mm [in]) = 0.64 [.025]

#### Mechanical Attachment:

- [Panel Attachment](#) = Without

#### Electrical Characteristics:

- Voltage Rating (VAC) = 250

#### Termination Related Features:

- [Solder Tail Contact Plating](#) = Tin
- Termination (Solder) Post Length (mm [in]) = 3.56 [0.140]

#### Body Related Features:

- [Narrow](#) = No
- [Post Number\(s\) Omitted](#) = None
- Solder Tail Contact Material = Copper Alloy

#### Contact Related Features:

- [Contact Centerline Spacing \(mm \[in\]\)](#) = 2.54 [0.100]
- [Contact Shape](#) = Square
- [Contact Mating Area Plating Material](#) = Tin
- [Contact Material](#) = Copper Alloy

#### Housing Related Features:

- Housing Color = Natural
- Housing Flammability Rating = UL 94V-0
- Housing Material = Polyester

#### Configuration Related Features:

- [Backwall/Post Interruption\(s\)](#) = Without

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

#### Conditions for Usage:

- [Terminate To](#) = Printed Circuit Board

#### Operation/Application:

- [Application](#) = Wire-to-Board

#### Other:

- Brand = AMP