

Product Details for 7014AD



7014AD

Tyco Part Number:
1423160-4
 [Active](#)

Time Delay Relays

[Not ELV or RoHS Compliant](#)

Product Highlights:

- ? 7000 Electropneumatic Timing Series
- ? Time Delay Relay
- ? Input Voltage = 120 VAC
- ? Input Voltage = 110 VAC
- ? Contact Arrangement = 4 Form C, 4PDT, 4 C/O

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us](#)
- [About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? None Available

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? [7000 Series 4 - Pole Timing Relay](#) (PDF, English)

CAD Files:

- ? None Available

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features

(Please use the Product Drawing for all design activity)

Product Type Features:

- ? Product Type = Time Delay Relay
- ? Termination Type = Screw Terminal

Electrical Characteristics:

- ? Input Voltage (VAC) = 110, 120
- ? Contact Rating = 10A @ 240 VAC

Body Related Features:

- ? [Series](#) = 7000 Electropneumatic Timing

Contact Related Features:

- ? Mounting Options = Panel Mount
- ? Mode of Operation = On-Delay
- ? Delay Time = 10 seconds to 100 seconds
- ? Type of Control = Knob
- ? Repeatability, Max. = $\pm 10\%$
- ? Approved Standards = CE Approved, CSA Certified, FM Approved, UL Listed
- ? Approx. Dimensions (L x W x H) (mm [in]) = 114.80 x 65.30 x 71.90 [4.523 x 2.572 x 2.832]

Configuration Related Features:

- ? [Contact Arrangement](#) = 4 Form C, 4PDT, 4 C/O
- ? Multiple Timing Ranges = Without

Industry Standards:

- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- ? Temperature Range (°C) = -30 – +75

Other:

- ? Brand = Agastat