

Product Details for 796433 - 1



796433 - 1

[Active](#)

CPC Connectors

[Not ELV or RoHS Compliant](#) [\(Find RoHS Compliant Alternates\)](#)

Product Highlights:

- ? Connector
- ? 7 Position
- ? Receptacle
- ? Pin
- ? Preloaded

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [RECEPTACLE ASSY, POSTED, STD SEX, SERIES 1, SIZE 13 - ...](#)
(PDF, English)

Catalog Pages/Data Sheets:

- ? [CIRCULAR CONNECTORS FOR COMMERCIAL SIGNAL AND POWER ...](#) (PDF, English)

Product Specifications:

- ? None Available

Application Specifications:

- ? [Circular Plastic Connectors \(CPC\)](#) (PDF, English)

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Number of Positions](#) = 7
- ? [Gender](#) = Receptacle
- ? [Pin/Socket](#) = Pin
- ? [Shell Size](#) = 13
- ? [Shell Type](#) = All Plastic
- ? [Product Series](#) = Series 1
- ? [Sealed](#) = No
- ? Mounting Hole Diameter (mm [in]) = 3.18 [0.125]

Mechanical Attachment:

- ? [Preloaded](#) = Yes
- ? [VDE Tested](#) = No
- ? Panel Attachment Method = Square Flange
- ? Keying = A

Termination Related Features:

- ? [Shell Thread Size](#) = 3/4 - 20 UNEF - 2A
- ? Termination Post Length (mm [in]) = 5.59 [0.220]

Body Related Features:

- ? [Mount Style](#) = Mounting Holes

Contact Related Features:

- ? [Contact Mating Area Plating](#) = Gold over Nickel
- ? [Contact Termination Area Plating](#) = Tin -Lead over Copper
- ? [Standard or Reverse Gender](#) = Standard
- ? Contact Type = Posted
- ? Contact Material = Copper Alloy

Housing Related Features:

- ? Housing Material = Nylon
- ? Housing Color = Black
- ? Housing Flammability Rating = UL 94V -0

Configuration Related Features:

- ? [Reverse Numbering](#) = Without

Industry Standards:

- ? [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C

Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board

Other:

- ? Brand = AMP