


Product Details for 87633 - 5



No Image Available

87633 - 5

[Active](#)

.156 Inch AMPMODU .031 X .062 Mod I

[RoHS Compliant](#) (Statement of Compliance)

Product Highlights:

- ? Header
- ? Vertical Mount Angle
- ? Gold (15) over Nickel (50) Contact Mating Area Plating
- ? Keyed
- ? Number of Positions = 5

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [HEADER ASSEMBLY, MOD I, VERTICAL, SINGLE ROW, .156@22](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? [Interconnection System, AMPMODU Mod I, High Pressure](#) (PDF, English)

Application Specifications:

- ? None Available

Instruction Sheets:

- ? [AMPMODU* HEADER ASSEMBLIES \(WITH MOD I POSTS\)](#) (PDF, English)

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Header
- ? Mount Angle = Vertical
- ? [Keyed](#) = Yes
- ? [Number of Positions](#) = 5

Mechanical Attachment:

- ? [Mating Post Length \(mm \[in\]\)](#) = 10.29 [0.405]

Termination Related Features:

- ? Termination End Plating = Gold Flash over Nickel (50)

Body Related Features:

- ? Number of Rows = Single
- ? Centerline (mm [in]) = 3.96 [0.156]
- ? Number of Keys = 2

Contact Related Features:

- ? Contact Mating Area Plating = Gold (15) over Nickel (50)
- ? Contact Material = Brass

Housing Related Features:

- ? Housing Material = Polyester (PBT)
- ? Housing Color = Black
- ? Housing Flammability Rating = UL 94V -0

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? Terminate To = Printed Circuit Board

Other:

- ? Brand = AMP