



### Product Compliance


[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JAN 2025 (247)</p> <p>Candidate List Declared Against: JAN 2025 (247)</p> <p>SVHC &gt; Threshold:</p> <p>Pb (4% in Component Part)</p> <p><b>Article Safe Usage Statements:</b>                      Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 1571987-5  
A201J1CQ004=DBL POLE, ROCKER



TE Part # 1571987-7  
A201J1ZQ004=DBL POLE, ROCKER



TE Part # 1571987-2  
A201J1AQ004=DBL POLE, ROCKER

## Customers Also Bought



TE Part #1-106506-2  
15P.HDP20 REC.ASSY.



TE Part #173924-1  
2 P ACTION PIN UMNL



TE Part #281695-8  
HEADER HE14 STRAIGHT 8 P




TE Part #7-1393243-9  
RT424730




TE Part #2-1614882-6  
CPF0603 10K 0.5% 25PPM 5K RL



TE Part #3-1625892-5  
3W SM M/OX 5% 27K



TE Part #1879642-1  
H8 100K 0.05% 15PPM



TE Part #7-1879684-5  
H8 6K81 0.1% 50PPM



TE Part #5-2337992-3  
RJ45 JACK MAG. POE 10/100 LED 1X1 INV.



TE Part #6-5530843-5  
CONN SEC II 31 POS 100C/L

## Documents

### Product Drawings

[A201J61ZQ0004=DBL POLE,ROCKER](#)

English

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_1-1571987-9\\_A.3d\\_igs.zip](#)

English



**Customer View Model**

[ENG\\_CVM\\_CVM\\_1-1571987-9\\_A.3d\\_stp.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_1-1571987-9\\_A.2d\\_dxf.zip](#)

English

[3D PDF](#)

[3D](#)

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Datasheets & Catalog Pages**

[GEMINI\\_SERIES\\_SWITCHES\\_QUICK\\_REF\\_GUIDE\\_2-1773458-5](#)

English