

5953398-1 Product Details

Have a Question?

Chat with a Product Information Specialist



Smart Card Connectors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Connector
- 8 Positions
- Without Card Guide Slots
- Not Stacked
- Height Above PC Board = 8.80 mm

[View all Features](#)

5953398-1

TE Internal Number: 5953398-1

Active

[View 3D PDF](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [smart card reader pcb mount through hole](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: [\(CAD Format & Compression Information\)](#)

- [2D Drawing](#) (DXF, Version A)
- [3D Model](#) (IGES, Version A)
- [3D Model](#) (STEP, Version A)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Card Guide Slots = Without
- Stacked = No
- Profile = Standard
- Card Type = Smart Card

Mechanical Attachment:

- Boardlock = With

Termination Related Features:

- Solder Tail Contact Plating = Tin over Nickel

Body Related Features:

- Number of Positions = 8
- Mount Style = Through-Hole
- [Card Scoop](#) = Without
- Card Thickness (mm [in]) = 0.76 [0.030]
- Switch Style = Unsealed
- Number of Signal Contacts = 8
- Number of Switch Contacts = 2
- Durability Rating = 30,000 Cycles

Contact Related Features:

- Contact Base Material = Phosphor Bronze
- Contact Plating, Mating Area, Material = Gold (30)

Housing Related Features:

- Housing Color = Black
- Housing Material = PBT - GF

Configuration Related Features:

- Height Above PC Board (mm [in]) = 8.80 [0.346]
- Cable = Without
- Card Detection Switch = With
- Card Detection Switch Position = Normally Closed

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- PCB Thickness, Recommended (mm [in]) = 1.57 [0.062]

Other:

- Brand = AMP

BOOKMARK

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat with Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow Us On:



Visit Us On:

