

1052646-1 Product Details

[Share](#) [Print](#) [Email](#)


SMA/QMA RF Connectors

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Launcher
- RF Connector Type = SMA
- Jack
- Applies To Coaxial Cable
- Body Style = Straight

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

1052646-1

(2052-3359-02)

TE Internal Number: 1052646-1

 [Active](#)

[Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [SMA" STRAIGHT 2 HOLE FLANGE MOUNT JACK ACCEPT .036 ...](#) (PDF, English)

Catalog Pages/Data Sheets:

- [SMA Connectors](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Launcher
- [RF Connector Type](#) = SMA
- [Gender](#) = Jack
- [Body Style](#) = Straight
- [Number of Panel Mount Holes](#) = 2
- [Body Material](#) = Stainless Steel
- [Body Finish](#) = Passivated
- [Center Contact](#) = With
- [Pin Diameter Accepted \(mm \[in\]\)](#) = 0.91 [0.036]
- [Captivated Contacts](#) = With
- [Dielectric Material](#) = TFE Fluorocarbon

Mechanical Attachment:

- [Panel Mount Retention](#) = With
- [Panel Mount Retention Type](#) = Flange
- [Panel Attachment Style](#) = Rear Mount

Electrical Characteristics:

- [Frequency](#) = DC - 18 GHz
- [Insulation Resistance \(MΩ\)](#) = 10,000

Body Features:

- [Length \(mm \[in\]\)](#) = 9.53 [0.375]

Contact Features:

- [Center Contact Material](#) = Beryllium Copper
- [Center Contact Plating](#) = Gold

Configuration Features:

- [Captivation Method](#) = Mechanical

Industry Standards:

- [Government/Industry Qualification](#) = No
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

Conditions for Usage:

- [Applies To](#) = Coaxial Cable

Other:

- [Brand](#) = AMP
- [Comment](#) = Hermetic Terminals; Field replaceable.

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

