


## 929922-1 Product Details

[Share](#) [Print](#) [Email](#)


929922-1

TE Internal Number: 929922-1

 Active

 [View 3D PDF](#)

### Timer Contacts

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Contact
- Contact Type = Socket
- Standard Power-Timer Series
- Wire Range = 0.50-1.00<sup>2</sup> [20-17] mm [AWG]
- Accepts Wire Insulation Diameter, Range = 1.40 - 2.10 mm, 2.21 - 3.00 mm

[View all Features](#)

### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [STANDARD POWER TIMER CONTACT Standard Power Timer Ko... \(TIF, English\)](#)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version A11)
- [3D Model](#) (IGES, Version A11)
- [3D Model](#) (STEP, Version A11)

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Additional Product Images:

- [Line Drawing](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Product Type](#) = Contact
- Series = Standard Power-Timer
- Mating Area Interface Dimensions (mm [in]) = 4.75 x 0.81 [.187 x .032]
- [Wire/Cable Type](#) = Regular Wire
- Insulation Support = With

#### Body Features:

- [Wire Range \(mm \[AWG\]\)](#) = 0.50-1.00<sup>2</sup> [20-17]
- Single Wire Sealing System = Yes
- Insulation Type = FLK (Vehicle Cable Plastic), FLR (Thin Walled Cable)
- Cantilever Spring Material = Stainless Steel
- Single Seal Part No. = 963243-1, 963244-1

#### Contact Features:

- Contact Type = Socket
- [Contact Base Material](#) = CuFe2
- [Contact Plating, Mating Area, Material](#) = Pre-Tin

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- [Accepts Wire Insulation Diameter, Range \(mm \[in\]\)](#) = 1.40 - 2.10 [0.055 - 0.083], 2.21 - 3.00 [0.087 - 0.118]
- [Applies To](#) = Wire/Cable

#### Operation/Application:

- Cavity Plug Part No. = 100132-1

#### Packaging Features:

- [Packaging Method](#) = Loose Piece

#### Other:

- GET 0.64 Connector System = No
- Brand = AMP

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

