


## 1934338-1 Product Details

[Share](#) [Print](#) [Email](#)


1934338-1

TE Internal Number: 1934338-1

 **Active**

 [View 3D PDF](#)

### Z-PACK TinMan Connectors

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Board-to-Board Configuration = Right Angle
- Header
- Header Type = Fully Shrouded
- Connector Style = Plug
- Contact Type = Pin

[View all Features](#)

#### Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

 [Add to My Part List](#)
 [Request Sample](#)
 [Find Similar Products](#)
 [Buy Product](#)

#### Documentation & Additional Information

##### Product Drawings:

- None Available

##### Catalog Pages/Data Sheets:

- None Available

##### Product Specifications:

- [Z-PACK TinMan\\* Connector System](#) (PDF, English)

##### Application Specifications:

- [Z-PACK TinMan Connector System](#) (PDF, English)

##### Instruction Sheets:

- None Available

##### CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version 1)
- [3D Model](#) (IGES, Version 1)
- [3D Model](#) (STEP, Version 1)

##### Additional Information:

- [Product Line Information](#)

##### Related Products:

- [Tooling](#)

[List all Documents](#)

#### Product Features (Please use the Product Drawing for all design activity)

##### Product Type Features:

- Connector Type = Header
- PCB Mounting Orientation = Vertical
- PCB Mount Retention = With
- Termination Method to PC Board = Through Hole - Press Fit
- PCB Mount Alignment = Without
- Sealed = No
- UL File Number = E28476

##### Mechanical Attachment:

- Stackable = No

##### Electrical Characteristics:

- Data Rate (Gb/s) = 10.000
- Differential Impedance ( $\Omega$ ) = 100
- Contact - Rated Current (A) = 0.5
- Hot Pluggable = No
- Operating Voltage Reference = AC
- Operating Voltage (VAC) = 250

##### Termination Features:

- Tail Length (mm [in]) = 2.5 [0.098]

##### Body Features:

- Header Type = Fully Shrouded
- Number of Positions = 54
- Number of Signal Positions = 36
- Number of Rows = 9
- Number of Columns = 6
- PCB Mount Retention Type = Compliant Posts
- Centerline (mm [in]) = 1.91 [0.075]
- Row-to-Row Spacing (mm [in]) = 1.40 [0.055]
- Mating Retention = Without

##### Contact Features:

- Contact Type = Pin
- Contact Design = Rectangular Post
- Contact Base Material = Phosphor Bronze
- Contact Plating, Mating Area, Material = Gold
- Contact Plating, Mating Area, Thickness ( $\mu\text{m}$  [ $\mu\text{in}$ ]) = 0.76 [29.92]
- Tail Plating Material = Matte Tin
- Tail Plating, Thickness ( $\mu\text{m}$  [ $\mu\text{in}$ ]) = 0.5 [20]

##### Housing Features:

- Connector Style = Plug
- End Wall Location = Dual
- Housing Color = Black
- Mating Alignment = With
- Mating Alignment Type = Guide Slot
- Housing Material = Liquid Crystal Polymer (LCP)
- UL Flammability Rating = UL 94V-0

##### Configuration Features:

- Number of Pairs per Connector = 18
- Pairs per Column = 3
- Differential Signaling = With

##### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant
- Agency/Standard = UL
- UL Rating = Recognized
- UL Voltage Rating (VAC) = 250

##### Environmental:

- Operating Temperature ( $^{\circ}\text{C}$  [ $^{\circ}\text{F}$ ]) = -65 - +90 [-85 - +194]

##### Conditions for Usage:

- Board-to-Board Configuration = Right Angle
- PCB Thickness, Recommended (mm [in]) = 1.57 [0.062]

##### Operation/Application:

- Contact Transmits (Typical Application) = Signal (Data)

##### Packaging Features:

- Packaging Method = Tube

##### Other:

- Brand = Tyco Electronics

#### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

#### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

#### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage your Account](#)

#### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address 