

PT1MA-15-FR-420E-M6

✓ ACTIVE

MEAS | MEAS PT1

TE Internal #: 04-1103-0006

TE Internal Description: PT1MA-15-FR-420E-M6

4-20MA PT1 STRING POTENTIOMETER

[View on TE.com >](#)



Sensors > Position Sensors > Potentiometer Sensors > Cable Actuated Position Sensors > 4-20MA PT1 STRING POTENTIOMETER



Position Sensor Product Type: **Industrial String Potentiometer**

Full Stroke Range: **381 mm [15 in]**

Output Signal Type: **4 – 20 mA**

Accuracy: **±.18 % of Full Scale**

Repeatability: **.05 % of Full Scale**

[All 4-20MA PT1 STRING POTENTIOMETER \(316\)](#)

Features

Product Type Features

Position Sensor Product Type	Industrial String Potentiometer
------------------------------	---------------------------------

Body Features

Case Material	Aluminum + Polycarbonate
---------------	--------------------------

Dimensions

Full Stroke Range	381 mm[15 in]
-------------------	---------------

Usage Conditions

Accuracy	±.18 % of Full Scale
Operating Temperature Range	-18 – 93 °C[0 – 200 °F]

Operation/Application

Output Signal Type	4 – 20 mA
--------------------	-----------

Industry Standards

IP Rating	IP65
-----------	------

Other

Encoder Drive	No
Repeatability	.05 % of Full Scale
Measuring Cable	.019 Inch Dia Nylon-Coated Stainless Steel



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: Not Yet Reviewed SVHC > Threshold: 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one (5.3% in Component) Methanone, (diphenylphosphinyl)(2,4,6-trimethylphenyl)- (1% in Component) Pb (18% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | MEAS PT1



Cable Actuated Position Sensors(1370)

Customers Also Bought



TE Part #04-0760-0677
PT101-0100-113-4110



TE Part #04-0979-0072
PT9420-0250-121-1110



TE Part #04-0975-0215
PT9150-0200-121-2410



TE Part #SG1-80-3
STRING POT, 80 INCH RANGE




TE Part #SM2-12
STRING POT, 12.5 INCH RANGE




TE Part #CAT-CAPS0010
4-20MA PT1 STRING
POTENTIOMETER



TE Part #04-0847-0012
PT420-0060-111-1110



TE Part #9015010-0010
PIN,SPRING,1/16 X 5/16 LG,CRES



TE Part #04-0980-0501
PT8101-0010-1X1-X110-632218F

Documents

Datasheets & Catalog Pages

PT1MA

English