

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2023 (235) SVHC > Threshold: Pb (40% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought





TE Part #63711-2
TAB 187 MAG-MATE SLIM LN.



TE Part #146898-1
1FHP,64,30A/P,S,C,S09,11,14



TE Part #1623771-3
C3A 10K 5% AMMO PK



TE Part #5-1625812-9
3631C 18UH 20%



TE Part #4-1879132-2
RN 0402 24K3 0.1% 10PPM 1K RL



TE Part #1879339-8
CPF 0603 340K 1% 50PPM 1K RL




TE Part #1-1734595-1
1.0 WTB SR VT HDR 11 POS



TE Part #767171-1
MICTOR RECEPT ASSY, 38 POS.



TE Part #87623-1
MOD II POST PLTD 30 DPLX



TE Part #7-2176391-4
RQ 1206 71K5 0.1% 10PPM 5K RL

Documents

CAD Files

Customer View Model

[ENG_CVM_1-103336-3_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-103336-3_H.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-103336-3_H.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English