



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**

Element Type: **Wire Wound**

Power Rating: **7 W**

Resistance Class: **1kΩ – 1MΩ**

Resistance Value: **1.2K Ω**

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Power Rating	7 W
Resistance Class	1kΩ – 1MΩ
Resistance Value	1.2K Ω
Passive Component Tolerance	5 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	38 x 7 x 8 mm
------------------------------	---------------

Usage Conditions

--	--



Operating Temperature Range	-55 – 350 °C[-67 – 662 °F]
Temperature Coefficient	±200 ppm/°C

Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

SBCHE61K2J

1.2K ohm, Wire Wound, Power Resistor, 5 %, 7 W, ±200 ppm/°C, Axial-Leaded, Copper Termination, 38 x 7 x 8 mm, Loose Piece - Box, CGS SBC



TE Part # 1623728-3
BCHE 11 W 10R 5%



TE Part # 1-1623728-2
BCHE 11 W 22K 5%



TE Part # CAT-C339-SB19B
Wirewound Resistor: Vertical Mount



TE Part # 2-1623728-2
BCHE 11 W 47R 5%

Also in the Series | CGS SBC




Surface Mount Resistors(1)




Through-Hole Resistors(212)


Customers Also Bought



TE Part #2820253010
44A0111-20-5



TE Part #7-215079-6
MICRO-MATCH FOB.06P




TE Part #928814-1
250 FASTON TAB TPBR



TE Part #9-1462038-9
IM03DGR=IM RELAY 140mW 5V



TE Part #6-1625892-1
3W SM M/OX 5% 5K6



TE Part #9-2176089-7
RP 1J 0.166W 121K 0.1% 25PPM 1K RL




TE Part #2-2176186-8
CRGH1206 1% 22K 0.5W



TE Part #4-2176412-4
5W XSM M/OX 5% 330R



TE Part #5787834-1
STD USB TYPE B, VERTICAL, T/H



TE Part #826936-2
2P AMPMODU II STIFT LEI



Documents

Product Drawings

BCHE 7 W 1K2 5%

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1623732-4_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1623732-4_BA.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1-1623732-4_BA.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

High Power Resistor - Type SBC (Square Ceramic) Series - Tyco Electronics Passives

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English