




Automotive Parts > Automotive Connectors > Automotive Headers > High Pin Count Header



PCB Mount Orientation: **Horizontal**

Termination Method to PCB: **Through Hole - Solder**

Sealable: **No**

Centerline (Pitch): **2.2 mm [.087 in]**

Connector System: **Wire-to-Board**

[All High Pin Count Header \(43\)](#)

Features

Product Type Features

Connector Product Type	Housing
Mixed & Hybrid Header	No
Header Type	Fully Shrouded
Connector Shape	Rectangular
Sealable	No
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Signal Positions	40
Number of Sections	1
PCB Mount Orientation	Horizontal
Number of Positions	40
Number of Rows	2



Electrical Characteristics

Operating Voltage	12 VDC
Voltage Rating (Max)	12 VDC
Nominal Voltage Architecture	12 V

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Mating Tab Width	.64 mm[.025 in]
Mating Tab Thickness	.64 mm[.025 in]
Contact Type	Tab
Contact Mating Area Plating Material	Tin (Sn)

Termination Features

Termination Method to PCB	Through Hole - Solder
---------------------------	-----------------------

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Interface
PCB Mount Retention	Without
Mounting Holes	With
Mating Alignment	With
PCB Mount Alignment	Without

Housing Features

Centerline (Pitch)	2.2 mm[.087 in]
--------------------	-----------------

Dimensions

Connector Width	49.4 mm[1.945 in]
PCB Thickness (Recommended)	1.2 – 1.6 mm[.047 – .063 in]
Profile Height from PCB	15.5 mm[.61 in]
Connector Length	24.47 mm[.963 in]

Usage Conditions

Operating Temperature (Max)	125 °C[212 °F]
Operating Temperature Range	-30 – 150 °C[-22 – 302 °F]

Operation/Application

||
||
||



Shielded	No
Circuit Application	Signal

Packaging Features

Packaging Method	Tube
------------------	------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-T319-T273
TH/.025 CONNECTOR SYSTEM,
RECPT AND TAB



TE Part # 1318695-1
025 IDC LOCK HSG 40P



TE Part # CAT-T319-CH8172
TH/.025 CONNECTOR SYSTEM,
HOUSING



Also in the Series | 0.64/025 Connector System

Automotive Connector Caps & Covers
(6)

Automotive Connector Locks &
Position Assurance(1)

Automotive Housings(174)

Automotive Signal & Power Headers
(152)

Automotive Terminals(20)

Other Automotive Connector
Accessories(4)

Customers Also Bought

TE Part #CAT-SIGH262
Signal Header

TE Part #2322946-3
6POS,TAB0.63X0.63,HDR ASSY,90DEG

TE Part #1-967162-2
3pos MQS .63 header 90deg THR

TE Part #1564410-1
AXIAL SEAL 37 X 57

TE Part #7-1904107-4
V23201-R1001-A512

TE Part #2-2322946-5
2POS,TAB0.63X0.63,HDR ASSY,90DEG

TE Part #2356619-1
32POS,TAB0.64X0.64,HDR ASSY,
90DEG,SMD

Documents

Product Drawings
025 CAP HSG ASSY 40P

English

CAD Files
3D PDF

3D



Customer View Model

[ENG_CVM_CVM_1-1318384-3_F.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1318384-3_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1318384-3_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Crimping of 025 Receptacle Contact](#)

Japanese

[Application Specification](#)

Japanese

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English

[Instruction Sheet \(non U.S.\)](#)

Japanese