ER1739KJL ✔ ACTIVE


CGS | CGS ER


TE Internal #: 1-1623749-3

39K ohm, Wire Wound, Power Resistor, 5 %, 14 W, 0 – 60 ppm/°C, Axial-Leaded, Copper Termination, 53.5 x 8 mm, Loose Piece - Tray, CGS ER

View on TE.com >

Passive Components > Resistors > Through-Hole Resistors

Resistor Type: **Power Resistor**

Element Type: **Wire Wound**

Power Rating: **14 W**

Resistance Class: **1kΩ – 1MΩ**

Resistance Value: **39K Ω**

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1

Electrical Characteristics

Operating Voltage	750 V
Power Rating	14 W
Resistance Class	1kΩ – 1MΩ
Resistance Value	39K Ω
Passive Component Tolerance	5 %

Body Features

Lead Type	Axial-Leaded

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	53.5 x 8 mm

Usage Conditions

Operating Temperature Range	-55 – 200 °C[-67 – 392 °F]
Temperature Coefficient	0 – 60 ppm/°C

Packaging Features

Packaging Method	Loose Piece - Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 1623749-6
ER17 22K 5% LOOSE



TE Part # 1-1623746-3
ER74 1R0 5% AMMO PK



TE Part # 6-1623746-9
ER74 R05 10% AMMO PK



TE Part # 4-1623750-7
ER58 R22 5% AMMO



TE Part # 1623748-1
ER16 10R 5% LOOSE

Also in the Series | CGS ER



Through-Hole Resistors(168)

Customers Also Bought




TE Part #1SNG626152R0000
EP-SGL-PG11-GR-B



TE Part #5039304024
DR-25-1/2-0-SP




TE Part #803513-SF
FN2200B-50-34



TE Part #130625
TERM, PIDG, SPD, 12-10, M6



TE Part #8-215083-0
MICRO-MATCH MOW.10P




TE Part #1-532431-1
HDI RECP ASSY 3 ROW 210 POS



TE Part #1-770966-1
02P MINI UMNL R/A HDR ASSY AU



TE Part #1-770970-1
08P MINI UMNL R/A HDR ASSY LF



TE Part #1-1546306-6
16P.374" DR BARRIER STRIP

TE Part #903185-000
HVOT-20/7-A/U-4(S30)

Documents

Product Drawings

ER17 39K 5% LOOSE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1623749-3_BA1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1623749-3_BA1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1623749-3_BA1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

High Power Resistors - Type ER/ERV Series

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English