



Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Methanone, (diphenylphosphinyl)(2,4,6-trimethylphenyl)- (2% in Component) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts




TE Part # 3-1415547-0
[RP8CS024](#)

Customers Also Bought



TE Part #282834-2
[TERMI-BLOK PCB MOUNT, 90 2P.](#)



TE Part #282837-2
[TERMI-BLOK PCB MOUNT 2P](#)



TE Part #3-640440-2
[02P MTA100 CONN ASSY 22AWG RED](#)



TE Part #1393219-6
[PE014012](#)




TE Part #4-1393224-9
[RY211024](#)




TE Part #1676386-2
[RN 0805 5K23 0.1% 10PPM 1KRL](#)



TE Part #5-1676481-5
[CPF 0603 1K1 0.1% 25PPM 1K RL](#)



TE Part #5-2176390-3
[RQ 1206 4K02 0.1% 10PPM 5K RL](#)



TE Part #1-2372389-0
[MICRO MNL, HDR ASSY, SINGLE ROW, AU](#)



TE Part #5227699-3
[BNC PCB VERTICAL](#)

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- [ENG_CVM_CVM_1-1415538-4_A.2d_dxf.zip](#)
- English
- Customer View Model



[ENG_CVM_CVM_1-1415538-4_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1415538-4_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Definitions](#) [General Purpose Relays](#)

English

Agency Approvals

[VDE Certificate](#)

English