



Connectors > D-Shaped Connectors

Number of Positions: **25**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Panel**

Connector Mounting Type: **Panel Mount**

Centerline (Pitch): **1.27 mm [.05 in]**

Features

Product Type Features

|                                    |               |
|------------------------------------|---------------|
| Compatible With Discrete Wire Type | Stranded      |
| Connector & Housing Type           | Plug          |
| Connector System                   | Wire-to-Panel |
| Connector & Contact Terminates To  | Wire & Cable  |

Configuration Features

|                     |    |
|---------------------|----|
| Number of Positions | 25 |
|---------------------|----|

Body Features

|                        |                    |
|------------------------|--------------------|
| Shell Plating Material | Electroless Nickel |
| Insulation Color       | Black              |
| Flying Leads Length    | 457.2 mm[18 in]    |

Contact Features

|                                      |              |
|--------------------------------------|--------------|
| Contact Mating Area Plating Material | Gold (Au)    |
| Contact Base Material                | Copper Alloy |
| Contact Type                         | Pin          |
| Contact Current Rating (Max)         | 3 A          |
| Contact Options                      | Installed    |

Termination Features

|                                    |                            |
|------------------------------------|----------------------------|
| Termination Method to Wire & Cable | Preterminated Flying Leads |
|------------------------------------|----------------------------|

Mechanical Attachment

|                         |             |
|-------------------------|-------------|
| Connector Mounting Type | Panel Mount |
|-------------------------|-------------|

Housing Features



|                    |                 |
|--------------------|-----------------|
| Centerline (Pitch) | 1.27 mm[.05 in] |
|--------------------|-----------------|

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 125 °C[-67 – 257 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                     |        |
|---------------------|--------|
| Circuit Application | Signal |
|---------------------|--------|

Product Compliance


For compliance documentation, visit the product page on [TE.com](#)>

|                                               |                                                                                                                                                                                                                                                                                                                                                                                                                              |
|-----------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                                                                                                                                                                                                                                                                                                                    |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                                                                                                                                                                                                                                                                                                                    |
| China RoHS 2 Directive MIIT Order No 32, 2016 | 有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold                                                                                                                                                                                                                                                                                                                                                                      |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2025 (250)<br>Candidate List Declared Against: JAN 2024 (240)<br>SVHC > Threshold:<br>Pb (.2% in Component part)<br><b>Article Safe Usage Statements:</b><br>Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content                               | Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                                                                                                                                                                                                                                                                                                                             |
| Solder Process Capability                     | Wave solder capable to 265°C                                                                                                                                                                                                                                                                                                                                                                                                 |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



Documents

Datasheets & Catalog Pages  
MICRODOT Microminiature D Connectors  
English