




Automotive Parts > Automotive Connector Accessories > Automotive Connector Caps & Covers



Number of Positions: 20

Primary Product Color: **Black**

Protection & Strain Relief Accessory Type: **Cover**

Primary Product Material: **PBT GF15**

Cable Exit Angle: **90°**

Features

Product Type Features

Sealable	No
Protection & Strain Relief Accessory Type	Cover

Configuration Features

Number of Positions	20
---------------------	----

Body Features

Primary Product Color	Black
Primary Product Material	PBT GF15
Cable Exit Angle	90°

Mechanical Attachment

Strain Relief	Without
---------------	---------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

Serviceable	Yes
-------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Customers Also Bought




TE Part #F27596-000
MP-381191-5-8A




TE Part #440133-2
2.5MM,HSG,2POS



TE Part #929505-2
FF FLA-STE-GEG2X3P



TE Part #1379678-1
16W TAB HSG ASSY BLACK



TE Part #1393366-1
V23540X7000Y 21=GET-FEM TERM S



TE Part #1718760-1
MCON 1.2 LL TAB SWS SN



TE Part #1924968-3
Contact, male 0.64, 20 to 22 AWG



TE Part #1-2176339-8
CRGCQ 0603 270R 1%



TE Part #1-2236905-1
NANO TAB 0.5X0.4,TERMINAL



TE Part #742412-000
1330-0607-10

Documents

Product Drawings

[MQS ABDECKKAPP2X10P](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1-1534099-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1534099-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1534099-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English