




Passive Components > Resistors > Through-Hole Resistors > Wirewound Resistor: Horizontal Mount



Resistor Type: **Power Resistor**
Element Type: **Wire Wound**
Power Rating: **10 W**
Resistance Class: **Up to 1kΩ**
Resistance Value: **470 Ω**

[All Wirewound Resistor: Horizontal Mount \(152\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	750 V
Power Rating	10 W
Resistance Class	Up to 1kΩ
Resistance Value	470 Ω
Passive Component Tolerance	5 %

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

--	--



Passive Component Dimensions	48 x 10 x 9 mm
------------------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 250 °C[-67 – 482 °F]
Temperature Coefficient	±300 ppm/°C

Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C339-SQ1
[Wirewound Resistor: Vertical Mount](#)

Also in the Series | [CGS SQ](#)




[Through-Hole Resistors\(659\)](#)

Customers Also Bought



TE Part #60295-2
[FF 250 REC 22-18AWG TPBR](#)



TE Part #180907
[FF 250 REC HSG 2P NYLON NAT](#)




TE Part #180908
[FF 250 TAB HSG 2P NYLON NAT](#)



TE Part #350780-1
[04P UMNL CAP HSG](#)



TE Part #1-480703-2
[04P UMNL CAP HSG RED](#)



TE Part #1217861-1
[250 FASTON,PCB TAB,TCBR](#)



TE Part #CAT-T319-CH8172
[TH/.025 CONNECTOR SYSTEM, HOUSING](#)

Documents

[Product Drawings](#)
[SQP10 470R 5% WIRE](#)

English

[CAD Files](#)
[Customer View Model](#)
[ENG_CVM_CVM_1-1623795-1_BA.3d_stp.zip](#)



English

Customer View Model

[ENG_CVM_CVM_1-1623795-1_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1623795-1_BA.2d_dxf.zip](#)

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[4-1773460-6_RESISTIVE_SOLUTIONS_RAIL](#)

English

[1309350_PASSIVE_COMPONENT](#)

English

[High Power Resistors - Type SQ Series](#)

English

[8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS](#)

English