CFH500A56RJ ✔ ACTIVE


CGS | CGS CFH

TE Internal #: 1-1623821-4

56 ohm, Wire Wound, 5 %, Power Resistor, 500 W, 2 Terminations, Custom Termination, Loose Piece - Box, 30 mm [1.181 in] Height, CGS CFH

View on TE.com >

Passive Components > Resistors > Chassis Mount Resistors > Power Wirewound Resistor: Mineral, CFH



Resistor Type: **Power Resistor**

Resistance Class: **Up to 1kΩ**

Resistance Value: **56 Ω**

Power Rating: **500 W**

Element Type: **Wire Wound**

All Power Wirewound Resistor: Mineral, CFH (17)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1

Electrical Characteristics

Operating Voltage	2500 V
Resistance Class	Up to 1kΩ
Resistance Value	56 Ω
Power Rating	500 W
Passive Component Tolerance	5 %

Termination Features

Number of Terminations	2
Chassis Mount Resistor Termination Type	Custom Termination

Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Slots

Dimensions

Product Height	30 mm[1.181 in]
Product Length	160 mm[6.299 in]
Product Width	95 mm[3.74 in]

Packaging Features

Packaging Method	Loose Piece - Box

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 2-1623821-8
CFH 1100 120R 5% 300MM LEADS




TE Part # CAT-C339-C339
Power Wirewound Resistor: Mineral, CFH




TE Part # 2-1623821-7
CFH350 620R 5% 1000MM LEADS

Also in the Series | CGS CFH



Chassis Mount Resistors(21)

Customers Also Bought



TE Part #NB-PTCO-166
Pt100, 2.0x5.0, Class C, PTFD101C1A0




TE Part #T4151210004-003
RPC-M12-MR-4CON-PVC-1.5



TE Part #EN3750-475
TCTL-1-5/16-U



TE Part #3-644488-3
13P MTA100 SHRD HDR F/L R/A SN



TE Part #1623804-3
SQZ10 3R9 5% WIRE



TE Part #9-2176414-1
7W STD M/OX 5% 110K



TE Part #2307725-8
8P,2MM,B-B,REC,SRHZ,SMD,0.1AU,TR



TE Part #CAT-P851-T1
PCB Power Relay: 30 amp, Monostable DC



TE Part #6-103325-5
15 MODII HD SRRA B/A .100CL,LF

Documents

Product Drawings

CFH 500 56R 5% 300MM LEADS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1623821-4_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1623821-4_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1623821-4_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

Aluminium_Housed_Power_Resistors-Type_CFH_Series

English